

DEEP TOP ROLLING LADDER

Features:

- 20" or 30" Deep top platform
- 450 lb. rated capacity
- Perforated or Grip Strut tread
- Ships unassembled
- 1-1/16" Tubular steel construction
- Powder coat gray finish
- Spring-loaded casters 2 - 4 step models
- Step Lock 5 - 16 step models
- 7" deep steps
- Complies with applicable OSHA & ANSI standards



DEEP TOP ROLLING LADDER

PERFORATED				GRIP STRUT				# of Steps	Step Width	Platform Height	Overall Height	Platform W x L		Base W x D	
Grainger Stock #	Tri-Arc Model #	Grainger Stock #	Tri-Arc Model #	Grainger Stock #	Tri-Arc Model #	Grainger Stock #	Tri-Arc Model #					20"	30"	20"	30"
20" DEEP TOP		30" DEEP TOP		20" DEEP TOP		30" DEEP TOP									
WITHOUT HANDRAILS															
25NV79	KDSR002166-D2	25NV80	KDSR002166-D3	25NV76	KDSR002162-D2	25NV77	KDSR002162-D3	2	16"	20"	20"	16" x 20"	16" x 30"	20" x 29"	20" x 39"
25NV85	KDSR002246-D2	25NV86	KDSR002246-D3	25NV82	KDSR002242-D2	25NV83	KDSR002242-D3	2	24"	20"	20"	24" x 20"	24" x 30"	28" x 29"	28" x 39"
25NV91	KDSR003166-D2	25NV92	KDSR003166-D3	25NV88	KDSR003162-D2	25NV89	KDSR003162-D3	3	16"	30"	30"	16" x 20"	16" x 30"	20" x 37"	20" x 47"
25NV97	KDSR003246-D2	25NV98	KDSR003246-D3	25NV94	KDSR003242-D2	25NV95	KDSR003242-D3	3	24"	30"	30"	24" x 20"	24" x 30"	28" x 37"	28" x 47"
25NW04	KDSR004166-D2	25NW05	KDSR004166-D3	25NW01	KDSR004162-D2	25NW02	KDSR004162-D3	4	16"	40"	40"	16" x 20"	16" x 30"	23" x 45"	23" x 55"
25NW10	KDSR004246-D2	25NW11	KDSR004246-D3	25NW07	KDSR004242-D2	25NW08	KDSR004242-D3	4	24"	40"	40"	24" x 20"	24" x 30"	31" x 45"	31" x 55"
WITH HANDRAILS															
25NW16	KDSR102166-D2	25NW17	KDSR102166-D3	25NW13	KDSR102162-D2	25NW14	KDSR102162-D3	2	16"	20"	56"	16" x 20"	16" x 30"	20" x 29"	20" x 39"
25NW22	KDSR102246-D2	25NW23	KDSR102246-D3	25NW19	KDSR102242-D2	25NW20	KDSR102242-D3	2	24"	20"	56"	24" x 20"	24" x 30"	28" x 29"	28" x 39"
25NW28	KDSR103166-D2	25NW29	KDSR103166-D3	25NW25	KDSR103162-D2	25NW26	KDSR103162-D3	3	16"	30"	66"	16" x 20"	16" x 30"	20" x 37"	20" x 47"
25NW34	KDSR103246-D2	25NW35	KDSR103246-D3	25NW31	KDSR103242-D2	25NW32	KDSR103242-D3	3	24"	30"	66"	24" x 20"	24" x 30"	28" x 37"	28" x 47"
25NW40	KDSR104166-D2	25NW41	KDSR104166-D3	25NW37	KDSR104162-D2	25NW38	KDSR104162-D3	4	16"	40"	76"	16" x 20"	16" x 30"	23" x 45"	23" x 55"
25NW46	KDSR104246-D2	25NW47	KDSR104246-D3	25NW43	KDSR104242-D2	25NW44	KDSR104242-D3	4	24"	40"	76"	24" x 20"	24" x 30"	31" x 45"	35" x 55"
25NW52	KDSR105166-D2	25NW53	KDSR105166-D3	25NW49	KDSR105162-D2	25NW50	KDSR105162-D3	5	16"	50"	86"	16" x 20"	16" x 30"	23" x 52"	23" x 62"
25NW58	KDSR105246-D2	25NW59	KDSR105246-D3	25NW55	KDSR105242-D2	25NW56	KDSR105242-D3	5	24"	50"	86"	24" x 20"	24" x 30"	35" x 52"	35" x 62"
25NW64	KDSR106166-D2	25NW65	KDSR106166-D3	25NW61	KDSR106162-D2	25NW62	KDSR106162-D3	6	16"	60"	96"	16" x 20"	16" x 30"	27" x 60"	27" x 70"
1CJG9	KDSR106246-D2	25NW67	KDSR106246-D3	1CJH9	KDSR106242-D2	25NW66	KDSR106242-D3	6	24"	60"	96"	24" x 20"	24" x 30"	35" x 60"	35" x 70"
25NW72	KDSR107166-D2	25NW73	KDSR107166-D3	25NW69	KDSR107162-D2	25NW70	KDSR107162-D3	7	16"	70"	106"	16" x 20"	16" x 30"	27" x 66"	27" x 76"
1CJH1	KDSR107246-D2	25NW75	KDSR107246-D3	1CJJ1	KDSR107242-D2	25NW74	KDSR107242-D3	7	24"	70"	106"	24" x 20"	24" x 30"	35" x 66"	35" x 76"
1CJH2	KDSR108246-D2	25NW77	KDSR108246-D3	1CJJ2	KDSR108242-D2	25NW76	KDSR108242-D3	8	24"	80"	116"	24" x 20"	24" x 30"	35" x 73"	35" x 83"
Sourcing*	KDSR109246-D2	25NW79	KDSR109246-D3	Sourcing*	KDSR109242-D2	25NW78	KDSR109242-D3	9	24"	90"	126"	24" x 20"	24" x 30"	35" x 78"	35" x 88"
1CJH3	KDSR110246-D2	25NW81	KDSR110246-D3	1CJJ3	KDSR110242-D2	25NW80	KDSR110242-D3	10	24"	100"	136"	24" x 20"	24" x 30"	35" x 85"	35" x 95"
1CJH4	KDSR111246-D2	25NW83	KDSR111246-D3	1CJJ4	KDSR111242-D2	25NW82	KDSR111242-D3	11	24"	110"	146"	24" x 20"	24" x 30"	35" x 92"	35" x 102"
1CJH5	KDSR112246-D2	25NW85	KDSR112246-D3	1CJJ5	KDSR112242-D2	25NW84	KDSR112242-D3	12	24"	120"	156"	24" x 20"	24" x 30"	35" x 99"	35" x 109"
1CJH6	KDSR113246-D2	25NW87	KDSR113246-D3	1CJJ6	KDSR113242-D2	25NW86	KDSR113242-D3	13	24"	130"	166"	24" x 20"	24" x 30"	40" x 105"	40" x 115"
1CJH7	KDSR114246-D2	25NW89	KDSR114246-D3	1CJJ7	KDSR114242-D2	25NW88	KDSR114242-D3	14	24"	140"	176"	24" x 20"	24" x 30"	40" x 112"	40" x 122"
1CJH8	KDSR115246-D2	25NW91	KDSR115246-D3	1CJJ8	KDSR115242-D2	25NW90	KDSR115242-D3	15	24"	150"	186"	24" x 20"	24" x 30"	40" x 119"	40" x 129"



THE EXPERTS IN CLIMBING AND ACCESS

For more information, please contact your Grainger Representative or visit Grainger.com

