



EAN:	4013288227591	Size:	205x150x55 mm
Part number:	05004285001	Weight:	1160 g
Article number:	8009 Zyklus Pocket Set 4	Country of origin:	CZ
		Customs tariff number:	82041100

- 27-piece Zyklus Pocket set with bits, sockets, universal holder and extension
- Compact Zyklus ratchet with integrated bit magazine
- The magnetic direct mounting simultaneously turns the 3/8" ratchet into a bit ratchet screwdriver with 1/4" bit mounting
- Freely pivoting ratchet head with 5 predefined locking positions
- Fine tooth reversible ratchet (72 teeth) for a low return angle of only 5°
- Captive and freely swivelling bit magazine for easy removal and secure storage of the bits
- Universal holder with stainless steel sleeve and strong permanent magnet, can be used as extension
- Space-saving and safe storage in a textile box, which can also be docked onto the Wera 2go system

Comprehensive and space-saving ratchet/screwdriver combination. Compact Zyklus ratchet with bit magazine for the pocket. Magnetic direct mounting for 1/4" hex drive bits and 3/8" sockets. Rapid tool change thanks to the non-locking mounting. As the head is lockable at 0°, 15° and 90°, the tool can be used as a ratchet and as a ratchet screwdriver. The fine toothing with 72 teeth allows for a low return angle of 5°. Wide range of applications thanks to 12 bits integrated in the handle. The robust ratchet mechanism allows for ample torque. Perfect combination of a Zyklus ratchet with a 12-piece screwdriver set. The 75 mm long universal holder for 1/4" hex drive bits can be used as an extension. Including sockets in the commonest dimensions. In a textile box, which can be docked onto the Wera 2go system.



Web link
<https://www.wera.de/en/05004285001>

Wera - 8009 Zyklus Pocket Set 4
 05004285001 - 4013288227591

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Combination tool mounting




Zyklus Pocket



The magnetic direct mounting is suitable for 3/8" sockets as well as 1/4" bits without the need for an adapter.

With integrated bit magazine




A captive, freely swivelling bit magazine for 12 bits (1/4", 25 mm length) is integrated in the handle of the compact Zyklus ratchet.

Swivelling bit magazine



The swivelling bit magazine allows for the bits to be removed easily in almost any situation and cannot be lost. The bits are safely stored.

Freely pivoting ratchet head




The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Locking the ratchet head



Thanks to the sliding switch on both sides, the ratchet head can be locked at the pre-defined positions 0° as well as 15° and 90° to the right and left.

Small return angle



The fine toothing with 72 teeth allows for a low return angle of only 5° for working in constricted screwdriving situations.

Simple direction change



The Zyklus Pocket ratchet can be quickly and easily reversed for clockwise/anti-clockwise rotation in any position using the knurl.

Web link

<https://www.wera.de/en/05004285001>

Wera - 8009 Zyklus Pocket Set 4
05004285001 - 4013288227591

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

8009 Zyklus Pocket, 3/8" x 1/4" x 133 mm



1x 3/8" x 1/4" x 133 mm



8794 SB Zyklus extension with free-turning sleeve, short, 3/8", 3/8" x 125 mm



05003582001

1x 3/8" x 125 mm



893/1/1 Universal Bit Holder, 1/4" x 75 mm


05091103001¹⁾

1x 1/4" x 75 mm


¹⁾ Included in the set 8009 Zyklus Pocket Set 2 (05004281001).

8790 HMB Zyklus socket with 3/8" drive, 1/4" x 29 mm



05003569001

1x 1/4" x 29 mm

05003570001

1x 5/16" x 29 mm

05003572001

1x 3/8" x 29 mm

05003573001

1x 7/16" x 29 mm

05003574001

1x 1/2" x 29 mm

05003575001

1x 9/16" x 29 mm

05003553001

1x 8 x 29 mm

05003554001

1x 9 x 29 mm

05003555001

1x 10 x 29 mm

05003557001

1x 12 x 29 mm

05003559001

1x 14 x 29 mm

05003561001

1x 16 x 30 mm

851/1 BTZ bits, PH 1 x 25 mm



05056420001

1x PH 1 x 25 mm

05056422001

1x PH 2 x 25 mm

867/1 BTZ TORX® bits, TX 10 x 25 mm



05066120001

1x TX 10 x 25 mm

05066122001

1x TX 15 x 25 mm

800/1 BTZ bits, 0.8 x 5.5 x 25 mm



05056064001

1x 0.8 x 5.5 x 25 mm

05056068001

1x 1.2 x 6.5 x 25 mm

840/1 BTZ bits, 4 x 25 mm



05056684001

1x 4 x 25 mm

05056687001

1x 6 x 25 mm

Web link

<https://www.wera.de/en/05004285001>

Wera - 8009 Zyklus Pocket Set 4
05004285001 - 4013288227591

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

840/1 Z bits, 3/16" x 25 mm



05135075001

05135076001

1x 3/16" x 25 mm

1x 1/4" x 25 mm

868/1 Z Square-Plus bits, # 1 x 25 mm




05066405001

05066410001

1x # 1 x 25 mm

1x # 2 x 25 mm

Hook and Loop Fastener Strip 120, 120 x 50 mm



1x 120 x 50 mm

Web link

<https://www.wera.de/en/05004285001>

Wera - 8009 Zyklus Pocket Set 4
05004285001 - 4013288227591

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de