



EAN:	4013288104847	Size:	76x16x3 mm
Part number:	05024160001	Weight:	3 g
Article number:	967 L TORX® HF	Country of origin:	CZ
		Customs tariff number:	82041100

- L-keys for recessed TORX® screws
- The holding function on the long arm keeps screws securely on the tool
- BlackLaser for high corrosion protection and long service life
- Laser-engraved and thereby wear-resistant size markings

High quality L-keys for recessed TORX® screws. With holding function (HF) on the long arm to securely hold the screw on the tool. Comes with extra-long arm. The BlackLaser surface treatment provides outstanding surface protection, even against corrosion, and a long service life. The tools are quickly to hand thanks to the laser-engraved and thereby wear-resistant size markings on the L-keys.

Web link
<https://www.wera.de/en/05024160001>

Wera - 967 L TORX® HF
05024160001 - 4013288104847

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

TORX® HF profile



In tight assembly or disassembly situations, for example in engine compartments, it is not possible to securely hold the screw with the hand on the screwdriver, and the screw subsequently often gets lost. Lengthy searches or the loss of the screw (with the associated danger that could bring about) are the consequence. The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that the screw is securely held on the tool!

Size identification



The size of each L-key has been engraved by a laser. In addition Take it easy L-keys have a colour coding according to sizes - for simple and rapid accessing of the required tool. Making it easy to find the right tool.

Surface protection



L-keys with BlackLaser surface treatment for outstanding surface protection and long service life. High corrosion protection.

Further versions in this product family:



mm



mm



inch



inch

05024160001	TX 8	76	16	3"	5/8"
05024161001	TX 9	79	16	3 1/8"	5/8"
05024162001	TX 10	85	17	3 1/4"	21/32"
05024163001	TX 15	90	18	3 1/2"	23/32"
05024164001	TX 20	96	19	3 3/4"	3/4"
05024165001	TX 25	104	21	4 1/8"	27/32"
05024166001	TX 27	112	22	4 7/16"	29/32"
05024167001	TX 30	122	24	4 13/16"	1"
05024168001	TX 40	132	27	5 3/16"	1 1/16"

Web link

<https://www.wera.de/en/05024160001>

Wera - 967 L TORX® HF
 05024160001 - 4013288104847

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de