

Table 1.69 Homeline Load Center Accessories (cont'd.)

Description		Cat. No.	Schedule	
	Ground Bar Pack - PK9GTA, PK9GTA & Lug	PKGTALP1	DE3A	
	Ground Bar Pack - PK9GTA, PK18GTA & Lug	PKGTALP2	DE3A	
	Ground Bar Pack - PK15GTA, PK18GTA & Lug	PKGTALP3	DE3A	
	Insulator Kit for PK7GTA through PK27GTA	PKGTAB	DE3A	
Handle Padlock Attachment	For padlocking main circuit breakers in convertible load center, "OFF"	50–125 A	QOM1PA	DE2E
		100–225 A	QOM2PA	DE2E
Neutral Bonding Screw	For use on all Homeline and QO 125A convertible main load centers	4028344850K	DE5	
	For use on QO 150A-225A convertible main load centers	4028345850K	DE5	
Neutral / Ground Lugs	Field-installed for 14–2 AWG Al or 14–4 AWG Cu wire	LK70AN	DE3B	
	Field-installed for 6–2/0 AWG Al/Cu wire	LK100AN	DE3B	
	Field-installed for 14–2/0 AWG Al/Cu wire	LK125AN	DE3B	
	Field-installed for 4 AWG to 300 kcmil Al/Cu wire. Use in Series S, 150-225A QO load center or S03 and below, 150-225A HOM load center	LK225AN	DE3A	
	Field-installed for 4 AWG–300 kcmil Al/Cu wire. Use in Series S04, 150–225 A HOM load center	LK225ANHOM	DE3A	
Replacement Cover Directory Label	1 through 42 numbered universal replacement directory label for load center covers	LSDL	DE5	
Retaining Kit for Breakers Used as Back-fed Mains	Secures circuit breaker to interior when used as a back-fed main. For HOM612L100F/S, RB and HOM48L125GC, GRB load centers	HOM1RK	DE3C	
	Secures ONE circuit breaker right side of interior when used as a back-fed main For 100–125 A convertible main load centers, Series S01 and S02	HOM4RK2LA	DE3C	
	Secures ONE circuit breaker right side of interior when used as a back-fed main For 150–225 A convertible main load centers, Series S01 and S02	HOM4RK2HA	DE3C	
	Secures circuit breaker to interior when used as a back-fed main For 2P 150–200 A circuit breakers	HOM5RK	DE3C	
Service Entrance Barriers	QO / Homeline 1Ø 100–125 A QOM1 convertible main load centers	PKSB1LA	DE3A	
	QO / Homeline 1Ø 150–225 A QOM2 convertible main load centers	PKSB1HA	DE3A	
	Homeline back-fed main breaker applications	PKSB1HOMBF	DE3A	

Table 1.70: Homeline Load Center Replacement Covers

Spacers	Homeline Standard Covers		Homeline Mono Flat Covers
	Combination	Combination	Gray Covers
	Gray Covers	White Covers	
8	HOMC8UC	—	—
12	HOMC12UC	HOMC12UCW	—
20	HOMC20UC	HOMC20UCW	—
24	HOMC24UC	HOMC24UCW	—
30	HOMC30UC [5]	HOMC30UCW	—
40	—	HOMC40UCW	—
42	HOMC42UC	—	—
60	HOMC60UC	—	HOMCMF60UC



QO and Homeline Qwik-Grip Load Center Accessories

Table 1.71: Qwik-Grip Load Center Accessories

Description	Cat. No.	Schedule	
Qwik-Grip replacement shield	(1) Qwik-Grip shield	PKQGS	DE3A
Qwik-Grip fillers	(4) Qwik-Grip fillers	PKQGFP	DE3A
Qwik-Grip replacement insert	(1) Qwik-Grip insert	PKQGI	DE3A
Qwik-Grip assembly kit	(4) Qwik-Grip shields, (4) Qwik-Grip fillers	PKQGA	DE3A

[5] Extra long version available HOMC30UFL