



EAN: 4013288173980
Part number: 05004049001
Article number: 8100 SB 9

Size: 265x135x65 mm
Weight: 1630 g
Country of origin: CZ
Customs tariff number: 82041100

- Freely pivoting ratchet head with 5 predefined locking positions
- Fine-pitched with 72 teeth
- Small return angle of only 5°
- Free-turning sleeve for high working speeds
- With Take it easy tool finder: colour coding by size

Incredibly compact set arrangement with many tools in a minimum of space. A completely new ratchet set feeling thanks to the unique textile boxes that are very robust and durable. They can be positioned upright for tidy storage on the workshop shelf. Additional surface protection due to textile outer material. Low weight and volume for simpler mobility. Take it easy Tool Finder with colour coding according to sizes.



Web link
<https://www.wera.de/en/05004049001>

Wera - 8100 SB 9
05004049001 - 4013288173980


Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop "6 in 1"



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely




The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Textile boxes



The textile boxes offer dramatically improved portability, and are space-saving to boot! This means you can now carry the same collection of tools, in a much more compact and comfortable package. The hassle of running back and forth for the right tools has now become a thing of the past. And the much lower weight of a set makes carrying more convenient than ever before. The textile box including the tool will even survive a fall undamaged.

Web link

<https://www.wera.de/en/05004049001>

Wera - 8100 SB 9

05004049001 - 4013288173980

Wera Werkzeuge GmbH
Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Set contents:

8000 B Zyklop Speed Ratchet with 3/8" drive, 3/8" x 199 mm



05003550001 1x 3/8" x 199 mm



8790 HMB Zyklop socket with 3/8" drive, 1/4" x 29 mm



05003569001	1x	1/4" x 29 mm
05003570001	1x	5/16" x 29 mm
05003572001	1x	3/8" x 29 mm
05003573001	1x	7/16" x 29 mm
05003574001	1x	1/2" x 29 mm
05003575001	1x	9/16" x 29 mm
05003576001	1x	5/8" x 30 mm
05003577001	1x	11/16" x 30 mm
05003578001	1x	3/4" x 30 mm

8794 LB Zyklop extension with free-turning sleeve, long, 3/8", 3/8" x 200 mm



05003583001 1x 3/8" x 200 mm

8794 B Zyklop wobble extension, 3/8", 3/8" x 76 mm



05003584001 1x 3/8" x 76 mm



8784 B1 Zyklop bit adaptor, 3/8", 1/4" x 3/8" x 44 mm



05003590001 1x 1/4" x 3/8" x 44 mm



851/4 TZ bits, PH 1 x 50 mm



05059805001	1x	PH 1 x 50 mm
05059810001	1x	PH 2 x 50 mm
05059815001	1x	PH 3 x 50 mm

855/4 TZ bits, PZ 1 x 50 mm



05060005001	1x	PZ 1 x 50 mm
05060010001	1x	PZ 2 x 50 mm
05060015001	1x	PZ 3 x 50 mm

867/4 Z TORX® bits, TX 20 x 50 mm



05060134001	1x	TX 20 x 50 mm
05060135001	1x	TX 25 x 50 mm
05060136001	1x	TX 27 x 50 mm
05060137001	1x	TX 30 x 50 mm
05060138001 ¹⁾	1x	TX 40 x 50 mm

1) Hexagonal blade

840/4 Z bits, 3/16" x 50 mm



05135097001	1x	3/16" x 50 mm
05135098001	1x	7/32" x 50 mm
05135099001	1x	1/4" x 50 mm
05346288001	1x	5/16" x 50 mm

Web link

<https://www.wera.de/en/05004049001>

Wera - 8100 SB 9
05004049001 - 4013288173980

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

800/4 Z bits, 1 x 5.5 x 50 mm



05059330001

1x 1 x 5.5 x 50 mm



Web link

<https://www.wera.de/en/05004049001>

Wera - 8100 SB 9

05004049001 - 4013288173980

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de