Renewal Parts for Type BR Loadcenter Covers and Deadfronts

Single-Phase with Main Circuit Breakers

Catalog Number	Combination Covers	Surface Covers	NEMA 3R Covers	NEMA 3R Deadfronts	Catalog Number	Combination Covers	Surface Covers	NEMA 3R Covers	NEMA 3R Deadfronts
B4242DFN	315-003-28	—	—	—	**BR2040B150R**	—	—	BR3RDOOR8	BR3RDF11
B4242DR1N	—	—	Not available	—	**BR2040B200**	BRCOVC35	—	—	—
B4242DSN	—	315-003-27	—	—	**BR2040B200R**	—	—	BR3RDOOR9	BR3RDF11
B4242EFN	315-003-28	—	—	—	**BR2040H200**	BRCOVC35	—	—	—
B4242ESN	—	315-003-27	—	—	**BR2430B150**	BRCOVC40	—	—	—
BR1020B100RF	—	—	BR3RDOOR2	BR3RDF1	**BR2440B200**	BRCOVC41	—	—	—
BR1212B100	BRCOVC12	—	—	—	**BR3030BC100**	BRCOVC59			
BR1220B100	BRCOVC12	—	—	—	**BR3030B150**	BRCOVC40	—	—	—
BR1224B100R		—	BR3RDOOR2	BR3RDF1	**BR3030B150R**	—	—	BR3RDOOR10	BR3RDF12
BR1224B100SFG	47-37466			47-37469	**BR3030BC150**	BRCOVC40	—	—	—
BR1616B100	BRCOVC16	—	—	—	**BR3040B150**	BRCOVC40	—	—	—
BR1620B100	BRCOVC16	—	—	—	**BR3040B200**	BRCOVC41	—	—	—
BR1624B100	BRCOVC16	—	—	—	**BR3040B200R**	—	—	BR3RDOOR11	BR3RDF12
BR1624B100R	—	—	BR3RDOOR3	BR3RDF2	**BR3040H200**	BRCOVC41	—	—	—
BR1624B125	BRCOVC17	—	—	—	**BR304242F**	315-003-28	—	—	—
BR1630B150	BRCOVC29	—	—	—	**BR304242S**	—	315-003-27	—	—
BR1632B200	BRCOVC31	—	—	—	**BR4040B200**	BRCOVC44	—	—	—
BR2020B100	BRCOVC22	—	—	—	**BR4040BC200**	BRCOVC44	—	—	—
BR2024B100R	—	—	BR3RDOOR4	BR3RDF4	**BR4040B200R**	—	—	BR3RDOOR12	BR3RDF13
BR2024B125	BRCOVC23	—	—	—	**BR4040H200**	BRCOVC44	—	—	—
BR2024B125R	—	—	BR3RDOOR4	BR3RDF4	**BR4242B225**	BRCOVC53 (2)	—	—	—
BR2024H100	BRCOVC22	—	—	—	**BR4242B225R**	—	—	BR3RDOOR13	BR3RDF15
BR2030B150	BRCOVC32	—	—	—	**BR48B200RF**	—	—	BR3RDOOR15	BR3RDF14
BR2030B150R	—	—	BR3RDOOR8	BR3RDF11	**BR816B100**	BRCOVC10	—	—	—
BR2030H150	BRCOVC32	—	—	—	**BR816B150RF**	—	—	BR3RDOOR5	BR3RDF5
BR2040B150	BRCOVC40	—	—	—	**BR816B200RF**	—	—	BR3RDOOR6	BR3RDF5