



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	24.92 x 10.00 x 12.40
Case Weight (lbs)	12.79
Country of Origin	Taiwan
Lens	Clear
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Rubber Tips
Diopter	2.50
Base Curve	8
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Bouton® Optical Mag Readers™

Semi-Rimless Safety Readers with Black Frame, Clear Lens and Anti-Scratch Coating - +2.50 Diopter

- Magnification reader glasses are for the worker who needs to see up close
- The 30 mm wide "curved top" reading magnifier provides the worker with enough lens area to view his work throughout the day
- Durable nylon frame with extra wide latex-free rubber nose pads for more comfort when working up close
- Temples with soft rubber pads provide a secure fit
- 8 Base curve lens
- +2.50 Diopter
- Meets ANSI Z87.1+
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-10

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-25-0010	Black	Clear	Clear	AS	616314064630	01616314064639	02616314064638
250-25-0015	Black	Clear	Clear	AS	616314036118	01616314036118	02616314036118
250-25-0020	Black	Clear	Clear	AS	616314036125	01616314036125	02616314036125
250-25-0025	Black	Clear	Clear	AS	616314036132	01616314036132	02616314036132
250-25-0030	Black	Clear	Clear	AS	616314036149	01616314036149	02616314036149
250-25-0115	Black	Tinted	Gray	AS	616314036156	01616314036156	02616314036156
250-25-0120	Black	Tinted	Gray	AS	616314036163	01616314036163	02616314036163
250-25-0125	Black	Tinted	Gray	AS	616314036170	01616314036170	02616314036170
250-25-0130	Black	Tinted	Gray	AS	616314036187	01616314036187	02616314036187
250-25-1515	Black	Clear	Clear	AS/AF	616314186257	01616314186256	02616314186255
250-25-2020	Black	Clear	Clear	AS/AF	616314186264	01616314186263	02616314186262
250-25-2525	Black	Clear	Clear	AS/AF	616314186271	01616314186270	02616314186279

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated