




YGHC29C29 Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC29C29](#)

Copper Compression C Connector, 2/O AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 2/O AWG(Str) - 250 kcmil (Tap)



Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

- 4/O AWG
- 250 kcmil

Application

For Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Run Range	1/2 in-5/8 in
Conductor - Rod Run	• 1/2 in • 5/8 in
Conductor - Copper Str Run Range	2/O AWG-250 kcmil
Conductor - Copper Str Run	• 2/O AWG • 4/O AWG • 250 kcmil
Conductor - Copper Str Tap Range	2/O AWG-250 kcmil
Conductor - Copper Str Tap	• 2/O AWG

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	52.3 mm
Dimension - Height inch	2.06 in
Dimension - Height fraction	2-3/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - B Length inch	0.88 in
Dimension - Length Overall inch	0.88 in

General

Trade Name	HYTAP™
Die Index	997
Plated	N
Sub Brand	HYGROUND, HYTAP
UPC	781810221051
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810221051
UPC 14 Digit GTIN	00781810221051

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand