



QRP® PolyTuff®
Polyurethane Electrostatic Dissipative (ESD)
Glove - 4 mil

- Packaged for ISO 5 (Class 100) applications
- Tough, sheer PolyTuff polyurethane (1.5 mil) film affords a high degree of tactile sensitivity
- Tough solvent process polyurethane, sulfur-free, no carbon shedding
- Ergonomic Comfort Curve hand specific design
- Static dissipative 10(6) ohms
- For use with Class I and Class II static sensitive devices
- ESD safe compliance to ANSI/ESD S20.20-2014
- Compliant with ASTM and IEST-RP-CC005.3 standards
- RoHS Compliant



Technical Data

Color	Black
Sizes Available	S-XL
Packaging	Case
Packed	10 Bags/Case
Case Dimensions (in)	17.00 x 8.00 x 5.00
Case Weight (lbs)	2.50
Country of Origin	Japan
Polymer	Polyurethane
Grip	Smooth
Cuff	Straight
Length	12"
Powder	Powder Free
Thickness	4 Mil
Construction	Unsupported, ESD Safe
Certifications	TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ISO Cleanroom	ISO 5 (Class 100)
Static Control Property	Static Dissipative

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-06-30

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
27GS	Black	S	616314278006	10616314278003	20616314278000
27GM	Black	M	616314277993	10616314277990	20616314277997
27GL	Black	L	616314277986	10616314277983	20616314277980
27GXL	Black	XL	616314278013	10616314278010	20616314278017

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
27GS	Black	S	616314278006	10616314278003	20616314278000
27GM	Black	M	616314277993	10616314277990	20616314277997
27GL	Black	L	616314277986	10616314277983	20616314277980
27GXL	Black	XL	616314278013	10616314278010	20616314278017