

CFL Tubes

T5, T8 & T12 Compact Fluorescent



(continued)

Catalog Number	Model Number	UPC Code	Product Description	Base	Lumens	CCT (K)	Case/Pallet Qty	Dist. Center
479642	927871205701	046677479640	F32T8/TL965/ALTO 30PK	Medium Bipin	2600	6,500	30/1050	PA, CA, TN
536482	927871205708	046677536480	F32T8/TL965/ALTO TG 30PK	Medium Bipin	2600	6,500	30/1440	TN
T8 Linear Fluorescent Lamp (continued)								
236877	927874083505	046677236878	F96T8/TL835/HO/ PLUS ALTO	Recessed Double Contact	8,200	3,500	25/1200	PA
236885	927874084105	046677236885	F96T8/TL841/HO/PLUS ALTO 25/1	Recessed Double Contact	8,200	4,100	25/1200	PA, CA, TN
236893	927874085005	046677236892	F96T8/TL850/PLUS/HO/ALTO 25/1	Recessed Double Contact	8,100	5,000	25/1200	PA, CA, TN
236844	927874583505	046677236847	F96T8/TL835 PLUS ALTO 25/1	Medium Bipin	5,700	3,500	25/1200	PA, TN
236851	927874584106	046677236854	F96T8/TL841 PLUS ALTO 25/1	Medium Bipin	5,900	4,100	25/1200	PA, CA, TN
409094	927874584108	046677409098	F96T8/TL841 PLUS/ALTO TG 25PK	Medium Bipin	5,900	4,100	25/1200	TN
236869	927874585008	046677236861	F96T8/TL850 PLUS ALTO 25/1	Medium Bipin	5,780	5,000	25/1200	PA, CA, TN
209056	927942009520	046677209056	F32T8/TL950 SLV	Medium Bipin	2,000	5,000	25/1400	PA, CA, TN
407197	928022803325	046677367206	F15T8/CW 25PK	Medium Bipin	870	4,100	25/4000	PA, CA, TN
407205	928022805425	046677378233	F15T8/D 25PK	Medium Bipin	750	6,500	25/4000	PA, TN
T8 U bent Fluorescent Lamp								
378976	927860083002	046677378974	FB32T8/TL830/6 ALTO 20PK	Medium Bipin	2,800	3,000	20/400	PA, CA, TN
379008	927860083502	046677379001	FB32T8/TL835/6 ALTO 20PK	Medium Bipin	2,800	3,500	20/400	PA, CA, TN
379024	927860084102	046677379025	FB32T8/TL841/6 ALTO 20PK	Medium Bipin	2,800	4,100	20/400	PA, CA, TN
378802	927860085003	046677378806	FB32T8/TL850/6 ALTO 20PK	Medium Bipin	2,750	5,000	20/400	PA, CA, TN
204214	927860183601	046677204211	FB32T8/ADV835/6/XEW/ALTO 25W	Medium Bipin	2,400	3,500	20/400	PA
204230	927860184201	046677204235	FB32T8/ADV841/6/XEW/ALTO 25W	Medium Bipin	2,400	4,100	20/400	PA, CA, TN
204248	927860185101	046677204242	FB32T8/ADV850/6/XEW/ALTO 25W	Medium Bipin	2,350	5,000	20/400	PA
226712	927861283002	046677226718	FB31T8/TL830/ALTO 15/1	Medium Bipin	2,775	3,000	15/1080	PA
226720	927861283502	046677226725	FB31T8/TL835/ALTO 15/1	Medium Bipin	2,775	3,500	15/840	PA, CA, TN
226746	927861284101	046677226749	FB31T8/TL841/ALTO 15/1	Medium Bipin	2,775	4,100	15/840	PA, CA, TN
226761	927861383502	046677226763	FB29T8/TL835/EW/ALTO 15/1	Medium Bipin	2,775	3,500	15/840	PA
226779	927861384102	046677226770	FB29T8/TL841/EW/ALTO 15/1	Medium Bipin	2,775	4,100	15/1080	TN
T5 Linear Fluorescent Lamp								
162982	927893184102	046677162986	F54T5/841/HO/ALTO TG 40PK	Miniature Bipin	5,000	4,000	40/1000	PA, CA, TN
166868	927893185001	046677166861	F54T5/850/HO/ALTO TG	Miniature Bipin	5,000	5,000	40/1000	PA, CA, TN
230771	927990483022	046677230777	14W/830 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	1,350	3,000	40/5280	PA
230797	927990483522	046677230791	14W/835 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	1,350	3,500	40/4000	PA, CA, TN
230805	927990484022	046677230807	14W/841 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	1,350	4,200	40/8640	PA, CA, TN
230847	927990683022	046677230845	28W/830 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	2,900	3,000	40/2000	PA, TN
230854	927990683522	046677230852	28W/835 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	2,900	3,500	40/2640	PA, CA, TN
230862	927990684022	046677230869	28W/841 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	2,900	4,000	40/2000	PA, CA, TN
230813	927990883022	046677230814	F21T5/830/ALTO 40PK	Miniature Bipin	2,100	3,000	40/3520	PA
230821	927990883522	046677230821	F21T5/835 Min Bipin T5 HE ALTO UNP/40	Miniature Bipin	2,100	3,500	40/3520	PA, CA, TN
230839	927990884022	046677230838	F21T5/841/ALTO 40PK	Miniature Bipin	2,100	4,000	40/3520	PA, TN
406314	927991383531	046677406318	F28T5 835 HE EA ALTO 25W	Medium Bipin	2,900	3,500	40/1000	PA
414201	927991385031	046677414207	F28T5 850 HE EA ALTO 25W	Medium Bipin	2,800	5,000	40/1000	PA
220509	927991983531	046677220501	F54T5 835 HO EA ALTO 49W	Miniature Bipin	5,000	3,500	40/4320	PA
220525	927991984031	046677220525	F54T5 841 HO EA ALTO 49W	Miniature Bipin	5,000	4,000	40/2640	PA, CA
406496	927991985031	046677406493	F54T5 850 HO EA ALTO 49W	Miniature Bipin	5,000	5,000	40/2640	PA
290197	927992183022	046677290191	F24T5/830/HO/ALTO 40PK	Miniature Bipin	2,000	3,000	40/8640	PA
290205	927992183522	046677290207	24W/835 Min Bipin T5 HO ALTO UNP	Miniature Bipin	2,000	3,500	40/5280	PA, TN
290213	927992184022	046677290214	24W/841 Min Bipin T5 HO ALTO UNP	Miniature Bipin	2,000	4,000	40/8640	PA, TN
290221	927992683022	046677290221	39W/830 Min Bipin T5 HO ALTO UNP	Miniature Bipin	3,500	3,000	40/3520	PA, TN
290239	927992683522	046677290238	39W/835 Min Bipin T5 HO ALTO UNP	Miniature Bipin	3,500	3,500	40/3520	PA
290254	927992684022	046677290252	39W/841 Min Bipin T5 HO ALTO UNP	Miniature Bipin	3,500	4,000	40/3520	PA, CA
230888	927992783022	046677230883	F35T5/830 40PK	Miniature Bipin	3,650	3,000	40/2000	PA
230953	927992784022	046677230951	F35T5/841 40PK	Miniature Bipin	3,650	-	40/2000	PA
417816	927992883531	046677417819	F54T5/835/HO/XEW/ALTO/44W	Medium Bipin	4,520	3,500	40/4320	PA
417824	927992884031	046677417826	F54T5/841/HO/XEW/ALTO 44W	Medium Bipin	4,520	-	40/2640	TN
417832	927992885031	046677417833	F54T5/850/HO/XEW/ALTO/44W	Medium Bipin	4,500	-	40/4320	PA
290262	927993183022	046677290269	54W/830 Min Bipin T5 HO ALTO UNP	Miniature Bipin	5,000	3,000	40/2640	PA
290288	927993183522	046677290283	54W/835 Min Bipin T5 HO ALTO UNP	Miniature Bipin	5,000	3,500	40/2640	PA, TN
290833	927993184022	046677290832	54W/840 Min Bipin T5 HO ALTO UNP	Miniature Bipin	5,000	4,000	40/1000	PA, CA, TN
135103	927993185022	046677135102	F54T5/850/HO/ALTO 40PK	Miniature Bipin	5,000	5,000	40/2640	PA, CA, TN
147454	927993186522	046677147457	F54T5/865/HO/ALTO 40PK	Miniature Bipin	4,750	6,500	40/2640	PA, CA, TN
332411	928000503321	046677114633	F6T5/CW FAM/25	Miniature Bipin	295	-	25/18000	PA, CA
332478	9280001003321	046677114640	F8T5/CW PH 25PK	Miniature Bipin	400	-	25/6000	PA, CA, TN
332536	928001503332	046677115142	F13T5/CW PH 25PK	Miniature Bipin	820	4,100	25/4000	PA, TN
207035	928001508332	046677207038	F13T5/30U 25PK	Miniature Bipin	1,000	3,000	25/4000	PA
T5 Circular Fluorescent Lamp								
166017	927965083013	8711500640956	MASTER TL5 Circular 22W/830 1CT/10	2GX13	1,800	3,000	10/450	PA, TN
166009	927965084013	8711500642219	MASTER TL5 Circular 22W/840 1CT/10	2GX13	1,800	4,000	10/450	TN
165936	927965783013	8711500642790	MASTER TL5 Circular 55W/830 1CT/10	2GX13	4,200	3,000	10/270	PA, TN
165928	927965784013	8711500642516	MASTER TL5 Circular 55W/840 1CT/10	2GX13	4,200	4,000	10/180	PA, TN

● Stock Ready