



jalas® EXALTER 9955

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2011 S3, SRC, HRO

Learn more

LOW-CUT, WATER REPELLANT WITH LACES

This low-cut safety shoe has the features you need for most work situations, such as PTC-textile nail protection, toecap in aluminum and high-grip Vibram Nitrile rubber outsole. The midsole and JALAS FX3 Supreme multilayer insole together with the sock-like construction provide ultimate comfort. PORON® XRD™ shock-absorption prevents injuries to foot and back. The upper is water repellant, perfect for those who work in wet environments.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Polstered shaft edge
- Ventilating insole
- Stabilizator
- Water repellent
- Ergonomically shaped
- Soft
- Specially designed details
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)
- Free from animal-derived materials

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Sprain injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Environments with risk for outsole penetration, Clean environments

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION Exalter
UPPER MATERIAL Microfiber, Textile
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces
SHOELACES LENGTH 100 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.26 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2011
S3, SRC, HRO

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile
- Stabilizator
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
34	1.5	2.5	3.5	9955-34	6408487512728
35	2	3.5	4	9955-35	6408487512735
36	3	4	5	9955-36	6408487512742
37	4	5	6	9955-37	6408487512759
38	5	5.5	6.5	9955-38	6408487512766
39	6	6.5	7.5	9955-39	6408487512773
40	6.5	7.5	8.5	9955-40	6408487512780
41	7	8	9	9955-41	6408487512797
42	8	9	10	9955-42	6408487512803
43	9	9.5	11	9955-43	6408487512810
44	10	10.5	11.5	9955-44	6408487512827
45	10.5	11	12.5	9955-45	6408487512834
46	11	12	13	9955-46	6408487512841
47	12	13	14	9955-47	6408487512858

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.