



### G-Tek®

#### Hi-Vis Seamless Knit Polyester Glove with Hi-Vis Polyurethane Coated Flat Grip on Palm & Fingers

- Seamless knit polyester shell offers increased comfort, finger dexterity and breathability
- Polyurethane coatings take on the surface properties of the glove liner providing a tactile grip in dry and slightly oily conditions, ideal for applications that require dexterity for precise handling
- Hi-Vis coloring makes this product very easy to see
- Knit Wrist helps prevent dirt and debris from entering the glove
- Silicone free
- Pair bagged for ease of distribution
- ⚠️ **WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

### Applications

- Thin Coating, Good Grip for High Dexterity Handling
- Small Parts Handling
- Maintenance and Repair Operations
- Quality Control and Inspection



### Technical Data

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Color                | Hi-Vis Orange                                     |
| Sizes Available      | XS-2XL                                            |
| Packaging            | Pair Bagged Retail Ready                          |
| Packed               | 25 Dozen/Case                                     |
| Case Dimensions (in) | 24.80 x 11.81 x 18.11                             |
| Case Weight (lbs)    | 25.35                                             |
| Country of Origin    | China                                             |
| Liner Material       | Polyester                                         |
| Coating              | Polyurethane                                      |
| Coating Color        | Hi-Vis Orange                                     |
| Coating Coverage     | Palm & Fingers                                    |
| Grip                 | Flat                                              |
| Gauge                | 13                                                |
| Cuff                 | Knit Wrist                                        |
| Construction         | Coated Seamless Knit                              |
| Certifications       | Silicone Free                                     |
| Product Circularity  | Reusable / Launderable<br>Recycled via Terracycle |

### Performance Data

|                     |       |
|---------------------|-------|
| ANSI Abrasion Level | 4     |
| ANSI Puncture Level | 2     |
| EN 388              | 3131X |

### Care Instructions



KEY: ♻️ Made from recycled or bio-based ♻️ Launderable ♻️ Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-13

## SKU Information

| SKU          | COLOR         | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|--------------|---------------|------|--------------|----------------|----------------|
| 33-425OR/XS  | Hi-Vis Orange | XS   | 616314092114 | 01616314092113 | 02616314092112 |
| 33-425OR/S   | Hi-Vis Orange | S    | 616314092121 | 01616314092120 | 02616314092129 |
| 33-425OR/M   | Hi-Vis Orange | M    | 616314092138 | 01616314092137 | 02616314092136 |
| 33-425OR/L   | Hi-Vis Orange | L    | 616314092145 | 01616314092144 | 02616314092143 |
| 33-425OR/XL  | Hi-Vis Orange | XL   | 616314092152 | 01616314092151 | 02616314092150 |
| 33-425OR/XXL | Hi-Vis Orange | 2XL  | 616314092169 | 01616314092168 | 02616314092167 |