



On-Demand Gasket Kits

Clean Cuts. Correct Fit.
Anywhere.

When a Gasket Fails

Production can stop instantly. Waiting on replacements costs time and money. With ALLPAX, cut a precise gasket on the spot and restore service fast.



ALLPAX Heavy-Duty Gasket Cutting Kits

Designed for field and plant use, ALLPAX Extension-Style kits deliver repeatable accuracy for circular flanges, rings, and odd-shaped gaskets. A premium brass cutter block with engraved scale allows precise radius control, while chrome-plated extension bars provide cutting capacity up to 61 in. (1550 mm). Built for durability, portability, and consistent precision in real maintenance conditions.

Cuts	Range	Materials
Circular flanges, rings, and odd shapes	Standard up to 61 in. O.D. Metric up to 1550 mm O.D.	Rubber, Graphite, Teflon, Fiber-Reinforced



Standard Heavy-Duty Gasket Cutter Kits



Part No.	Description	Board	Extension Bar(s)
AX6000	Cuts 0 I.D. – 13" O.D. Gaskets		
AX6001	Cuts 0 I.D. – 25" O.D. Gaskets		•
AX6002	Cuts 0 I.D. – 37" O.D. Gaskets		•
AX6003	Cuts 0 I.D. – 49" O.D. Gaskets		•
AX6004	Cuts 0 I.D. – 61" O.D. Gaskets		•
AX6010	Cuts 0 I.D. – 13" O.D. Gaskets	•	
AX6020	Cuts 0 I.D. – 25" O.D. Gaskets	•	•
AX6030	Cuts 0 I.D. – 37" O.D. Gaskets	•	•
AX6040	Cuts 0 I.D. – 49" O.D. Gaskets	•	•
AX6050	Cuts 0 I.D. – 61" O.D. Gaskets	•	•

ALL KITS INCLUDE:

- Premium brass cutter block with engraved precision scale.
- Center pin handle
- Standard and heavy-duty cutting blades
- Dove-tail template
- Bolt hole locator
- Rugged storage case

Metric Heavy-Duty Gasket Cutter Kits



Part No.	Description	Board	Extension Bar(s)
AX6100	Cuts 0 I.D. – 330mm O.D. Gaskets		
AX6101	Cuts 0 I.D. – 635mm O.D. Gaskets		•
AX6102	Cuts 0 I.D. – 940mm O.D. Gaskets		•
AX6103	Cuts 0 I.D. – 1245mm O.D. Gaskets		•
AX6104	Cuts 0 I.D. – 1550mm O.D. Gaskets		•
AX6110	Cuts 0 I.D. – 330mm O.D. Gaskets	•	
AX6120	Cuts 0 I.D. – 635mm O.D. Gaskets	•	•
AX6130	Cuts 0 I.D. – 940mm O.D. Gaskets	•	•
AX6140	Cuts 0 I.D. – 1245mm O.D. Gaskets	•	•
AX6150	Cuts 0 I.D. – 1550mm O.D. Gaskets	•	•