



G-Tek® PolyKor®

Seamless Knit Polykor Blended Glove with Hi-Vis Impact Protection and Nitrile Foam Coated Palm & Fingers

- Seamless construction offers increased comfort and breathability
- Polykor blended shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Foam Nitrile coatings are breathable and durable, designed with a cell structure that disperse fluids on contact for an improved grip
- Thermo Plastic Rubber (TPR) back-of-hand impact resistance to knuckles and fingers by dispersing impact force energy away from the bone, without sacrificing dexterity
- Aramid reinforced thumb crotch for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Knit Wrist helps prevent dirt and debris from entering the glove
- **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring




Technical Data

Color	Hi-Vis Yellow
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	60 Pair/Case
Case Dimensions (in)	11.02 x 7.09 x 22.44
Case Weight (lbs)	38.29
Country of Origin	China
Liner Material	PolyKor
Coating	Nitrile
Coating Color	Orange
Coating Coverage	Palm & Fingers
Grip	Foam
Gauge	13
Cuff	Knit Wrist
Impact Protection	Finger, Thumb, Back of Hand
Construction	Coated Seamless Knit, Reinforced Thumb Crotch
Product Circularity	Reusable / Launderable

Performance Data

Cut Level	A3
ANSI Abrasion Level	4
ANSI Puncture Level	3
ANSI Impact Level	2
EN 388	4X42CP

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
HVY710HSNFB/S	Hi-Vis Yellow	S	662909013729	20662909013723	10662909013726
HVY710HSNFB/M	Hi-Vis Yellow	M	662909013736	20662909013730	10662909013733
HVY710HSNFB/L	Hi-Vis Yellow	L	662909013743	20662909013747	10662909013740
HVY710HSNFB/XL	Hi-Vis Yellow	XL	662909013750	20662909013754	10662909013757
HVY710HSNFB/2XL	Hi-Vis Yellow	2XL	662909013767	20662909013761	10662909013764