



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288095497 | <b>Size:</b>                  | 112x40x11 mm |
| <b>Part number:</b>    | 05027212001   | <b>Weight:</b>                | 102 g        |
| <b>Article number:</b> | 950 BM        | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82041100     |

- L-keys for hexagonal socket screws
- Hexagonal socket wrench with Hex-Plus advantage for a longer screw life
- Laser-engraved and thereby wear-resistant size markings
- BlackLaser for high corrosion protection and long service life
- Metric

High quality L-keys for hexagonal socket screws. Hex-Plus offers a larger contact surface within the screw head. This reduces the notching effects to a minimum and almost completely eliminates the risk of destroying the screw recess. The BlackLaser surface treatment provides outstanding surface protection, even against corrosion, and a long service life. Wear-resistant size markings for rapid accessing.

**Web link**  
<https://www.wera.de/en/05027212001>

Wera - 950 BM  
05027212001 - 4013288095497

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## L-Keys



We questioned the classic L-key design, since all too often the screw head recess is rounded out, meaning screws can no longer be tightened or loosened - and so the user finds the L-key slipping out of the recess. Wera Hex-Plus tools have a larger contact surface in the screw head. The notching effects are reduced and thereby the deformation of the screws. At the same time, as much as 20 % more torque can be applied.

## Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

## Size identification



The size of each L-keys has been engraved by a laser. In addition Take it easy L-keys have a colour coding according to sizes - for simple and rapid accessing of the required tool. Making it easy to find the right tool.

## Surface protection



L-keys with BlackLaser surface treatment for outstanding surface protection and long service life. High corrosion protection.

**Web link**  
<https://www.wera.de/en/05027212001>

Wera - 950 BM  
 05027212001 - 4013288095497

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)

## Further versions in this product family:

|                           |  |  |  |  |  |
|---------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                           | mm                                                                                | mm                                                                                | mm                                                                                | inch                                                                                | inch                                                                                |
| 05027201001 <sup>1)</sup> | 1.5                                                                               | 45                                                                                | 14                                                                                | 1 3/4"                                                                              | 9/16"                                                                               |
| 05027202001               | 2.0                                                                               | 50                                                                                | 16                                                                                | 2"                                                                                  | 5/8"                                                                                |
| 05027203001               | 2.5                                                                               | 56                                                                                | 18                                                                                | 2 7/32"                                                                             | 23/32"                                                                              |
| 05027204001               | 3.0                                                                               | 63                                                                                | 20                                                                                | 2 1/2"                                                                              | 25/32"                                                                              |
| 05027205001               | 3.5                                                                               | 66                                                                                | 23                                                                                | 2 5/8"                                                                              | 29/32"                                                                              |
| 05027206001               | 4.0                                                                               | 70                                                                                | 25                                                                                | 2 3/4"                                                                              | 1"                                                                                  |
| 05027207001               | 4.5                                                                               | 75                                                                                | 26                                                                                | 3"                                                                                  | 1 1/32"                                                                             |
| 05027208001               | 5.0                                                                               | 80                                                                                | 28                                                                                | 3 1/8"                                                                              | 1 3/32"                                                                             |
| 05027209001               | 6.0                                                                               | 90                                                                                | 32                                                                                | 3 1/2"                                                                              | 1 1/4"                                                                              |
| 05027210001               | 7.0                                                                               | 95                                                                                | 34                                                                                | 3 3/4"                                                                              | 1 5/16"                                                                             |
| 05027211001               | 8.0                                                                               | 100                                                                               | 36                                                                                | 4"                                                                                  | 1 7/16"                                                                             |
| 05027213001               | 9.0                                                                               | 106                                                                               | 38                                                                                | 4 11/64"                                                                            | 1 1/2"                                                                              |
| <b>05027212001</b>        | <b>10.0</b>                                                                       | <b>112</b>                                                                        | <b>40</b>                                                                         | <b>4 7/16"</b>                                                                      | <b>1 9/16"</b>                                                                      |
| 05027214001               | 11.0                                                                              | 120                                                                               | 43                                                                                | 4 23/32"                                                                            | 1 11/16"                                                                            |
| 05027215001               | 12.0                                                                              | 125                                                                               | 45                                                                                | 5"                                                                                  | 1 49/64"                                                                            |

1) Regular hexagon

## Web link

<https://www.wera.de/en/05027212001>

Wera - 950 BM

05027212001 - 4013288095497

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)