
RATCHET-PRO™ SERIES FLOOR BOXES

Ratchet-Pro Series Floor Box Cover Plate Ordering Information


Brass/Brushed Aluminum Duplex Cover Plate



PART NUMBERS:
895 (Brass)
895TCAL (Brushed Aluminum)

With flip lids, 5 1/2" (140mm) diameter for carpet.


Brass/Brushed Aluminum Duplex Cover Plate



PART NUMBERS:
895T (Brass)
895TAL (Brushed Aluminum)

With flip lids, 4 1/4" (105mm) diameter for tile.

Brass/Brushed Aluminum Cover Plate




PART NUMBERS:
895SP (Brass)
895SPCAL (Brushed Aluminum)

With two screw plug openings, 5 1/2" [140mm] diameter for carpet.

NOTE: Screw plug openings are 1 1/2" (38mm) - 16 tapped openings.


895TSP Brass Cover Plate



With two screw plug openings, 4 1/4" (108mm) diameter for tile.

NOTE: Screw plug openings are 1 1/2" (38mm) - 16 tapped openings.


Brass/Brushed Aluminum GFI Receptacle Cover Plate



PART NUMBERS:
895GFI (Brass)
895GFICAL (Brushed Aluminum)

5 1/2" (140mm) diameter for carpet.


Brass/Brushed Aluminum GFI Receptacle Cover Plate



PART NUMBERS:
895TGFI (Brass)
895TGFIAL (Brushed Aluminum)

4 1/4" (108mm) diameter for tile.


896 Brass Communication or Power Cover Plate



With 2 5/8" (67mm) threaded opening, 5 1/2" (140mm) diameter for carpet.

NOTE: Sold without abandon plug.


896T Brass Communication or Power Cover Plate



With 2 5/8" (67mm) threaded opening, 4 1/4" (108mm) diameter for tile.


NOTE: Sold without abandon plug.

896CK Brass Communication or Power Cover Plate




With 2 1/4" (57mm) threaded opening, 5 1/2" (140mm) diameter for carpet.

896TCK Brass Communication or Power Cover Plate



With 2 1/4" (57mm) threaded opening, 4 1/4" (108mm) diameter for tile.


Brass/Brushed Aluminum Cover Plate



PART NUMBERS:
896CK-1/2 (Brass)
896CKAL-1/2 (Brushed Aluminum)

With 1/2" (12.7mm) threaded opening, 5 1/2" (140mm) diameter for carpet.

Brass/Brushed Aluminum Cover Plate



PART NUMBERS:
896TCK-1/2 (Brass)
896TCKAL-1/2 (Brushed Aluminum)


With 1/2" (12.7mm) threaded opening, 4 1/4" (108mm) diameter for tile.

NOTE: All cover plates are furnished with gasket and three screws.
The 895P Polycarbonate Series Cover Plates must be field modified for dual service.

880 SERIES™ FLOOR BOXES

880 Series Floor Box Cover Plates Ordering Information


Duplex Cover Plate with Flip Lid



PART NUMBERS:
895 (Brass)
895TCAL (Brushed Aluminum)

Duplex cover plate with flip lids, 5 1/2" (140mm) for carpet.


Aluminum Duplex Power Plate



PART NUMBERS:
895TGFI (Brass)
895TGFIAL (Brushed Aluminum)

GFI receptacle cover plate, 4 1/4" (108mm) for tile.


Aluminum Duplex Cover Plate



PART NUMBERS:
895TCAL-BK (Black)
895TCAL-GY (Gray)
895TCAL-NK (Nickel)
895TCAL-BS (Brass)
895TCAL-BZ (Bronze)

With flip lids, 5 1/2" (140mm) diameter for carpet.


Nonmetallic Duplex Power Plate



PART NUMBERS:
895P-BLK (Black)
895P-BRN (Brown)
895P-BRZ (Bronze)
895P-AL (Brass)

Polycarbonate duplex cover plate with flip lids for carpet.


Duplex Cover Plate with Flip Lids



PART NUMBERS:
895T (Brass)
895TAL (Brushed Aluminum)


Duplex cover plate with flip lids, 4 1/4" (108mm) for tile.

896 Communication or Power Cover Plate




Brass communication or power cover plate with 2 5/8" (67mm) threaded opening for carpet. Sold without abandon plug.

895SP Cover Plate With Two Screw Plug Openings




Cover plate with two 1 1/2" (38mm) screw plug openings, 5 1/2" (140mm) for carpet.

896T Communications or Power Cover Plate




Brass communications or power cover plate with 2 5/8" (67mm) threaded opening for tile. Sold without abandon plug.

895TSP Cover Plate With Two Screw Plug Openings




Brass cover plate with two 1 1/2" (38mm) screw plug openings, 4 1/4" (108mm) for tile.

896CK Communications or Power Cover Plate



Brass communications or power cover plate with 2 1/4" (57mm) threaded opening for carpet.


GFI Receptacle Cover Plate



PART NUMBERS:
895GFI (Brass)
95GFICAL (Brushed Aluminum)

GFI receptacle cover plate, 5 1/2" (140mm) for carpet.

896TCK Communications or Power Cover Plate




Brass communications or power cover plate with 2 1/4" (57mm) threaded opening for tile.

861 SERIES™ FLOOR BOXES

861 Series Floor Box Cover Plate Ordering Information


Duplex Cover Plate With Flip Lids



PART NUMBERS:
895 (Brass)
895TCAL (Brushed Aluminum)

Duplex cover plate with flip lids, 5 1/2' (140mm) for carpet.


GFI Receptacle Cover Plate



PART NUMBERS:
895GFI (Brass)
895GFICAL (Brushed Aluminum)

GFI receptacle cover plate, 5 1/2" (140mm) for carpet.


Duplex Cover Plate With Flip Lids



PART NUMBERS:
895T (Brass)
895TAL (Brushed Aluminum)

Duplex cover plate with flip lids, 4 1/4" (108mm) for tile.


GFI Receptacle Cover Plate



PART NUMBERS:
895TGFI (Brass)
895TGFIAL (Brushed Aluminum)

GFI receptacle cover plate, 4 1/4" (108mm) for tile.


Cover Plate With Two Screw Plug Openings



PART NUMBERS:
895SP (Brass)
895SPAL (Brushed Aluminum)

Cover plate with two screw plug openings, 5 1/2" (140mm) for carpet.


Duplex Cover Plate



PART NUMBERS:
895P-BLK (Black)
895P-BRN (Brown)
895P-BRZ (Bronze)
895P-AL (Brushed Aluminum)


Polycarbonate duplex cover plate with flip lids for carpet.

895TSP Cover Plate with Two Screw Plug Openings



Brass cover plate with two screw plug openings, 4 1/4" (108mm) for tile.

Aluminum Duplex Cover Plate



PART NUMBERS:
895TCAL-BK (Black)
895TCAL-GY (Gray)
895TCAL-NK (Nickel)
895TCAL-BS (Brass)
895TCAL-BZ (Bronze)


With flip lids, 5 1/2" (140mm) diameter for carpet.

NOTE: All 895 Style Cover Plates are furnished with gasket and three screws.
All carpet cover plates are 5 1/2" (140mm) in diameter.
All tile cover plates are 4 1/4" (108mm) in diameter.

862 SERIES™ FLOOR BOXES

862 Series Floor Box Cover Plate Ordering Information


Duplex Cover Plate With Flip Lids



PART NUMBERS:
895 (Brass)
895TCAL (Brushed Aluminum)

Duplex cover plate with flip lids, 5 1/2' (140mm) for carpet.


GFI Receptacle Cover Plate



PART NUMBERS:
895GFI (Brass)
895GFICAL (Brushed Aluminum)

GFI receptacle cover plate, 5 1/2" (140mm) for carpet.


Duplex Cover Plate With Flip Lids



PART NUMBERS:
895T (Brass)
895TAL (Brushed Aluminum)

Duplex cover plate with flip lids, 4 1/4" (108mm) for tile.


GFI Receptacle Cover Plate



PART NUMBERS:
895TGFI (Brass)
895TGFIAL (Brushed Aluminum)


GFI receptacle cover plate, 4 1/4" (108mm) for tile.

895SP Cover Plate With Two Screw Plug Openings



Cover plate with two screw plug openings, 5 1/2" (140mm) for carpet.


Duplex Cover Plate



PART NUMBERS:
895P-BLK (Black)
895P-BRN (Brown)
895P-BRZ (Bronze)
895P-AL (Brushed Aluminum)


Polycarbonate duplex cover plate with flip lids for carpet.

895TSP Cover Plate with Two Screw Plug Openings



Brass cover plate with two screw plug openings, 4 1/4" (108mm) for tile.

Aluminum Duplex Cover Plate



PART NUMBERS:
895TCAL-BK (Black)
895TCAL-GY (Gray)
895TCAL-NK (Nickel)
895TCAL-BS (Brass)
895TCAL-BZ (Bronze)

With flip lids, 5 1/2" (140mm) diameter for carpet.


NOTE: All 895 Style Cover Plates are furnished with gasket and three screws.
All carpet cover plates are 5 1/2" (140mm) in diameter.
All tile cover plates are 4 1/4" (108mm) in diameter.

FIRE CLASSIFIED FLOOR BOXES

880MP Series Floor Boxes

Cover Plates for 881FC Floor Box


Duplex Cover Plate



PART NUMBERS:
895 (Brass)
895TCAL (Brushed Aluminum)

With flip lids, 5 1/2" (140mm) diameter for carpet.


GFI Receptacle Cover Plate



PART NUMBERS:
895TGFI (Brass)
895TGFIAL (Brushed Aluminum)

4 1/4" (108mm) for tile.


Duplex Cover Plate



PART NUMBERS:
895T (Brass)
895TAL (Brushed Aluminum)

With flip lids, 4 1/4" (108mm) for tile.


Aluminum Duplex Cover Plate



PART NUMBERS:
895TCAL-BK (Black)
895TCAL-GY (Gray)
895TCAL-BS (Brass)
895TCAL-NK (Nickel)
895TCAL-BZ (Bronze)

With flip lids, 5 1/2" (140mm) diameter for carpet.

GFI Receptacle Cover Plate



PART NUMBERS:
895GFI (Brass)
895GFICAL (Brushed Aluminum)


5 1/2" (140mm) diameter for carpet.

NOTE: 1. **All cover plates are furnished with gasket and three screws.**
2. **Polycarbonate cover plates cannot be used on the 881FC Fire Classified Floor Box.**

CAUTION

Installation must comply with NEC and local code conductor volume requirements. Not for use when concrete is the finished floor. Use only for tile, carpet or wood covered floors.

Ratchet-Pro Fire Classified Floor Boxes Installation Cross Section



NOTE: UL Listed for tile, terrazzo, polished concrete, wood and carpet floors.