



EAN:	4013288196217	Size:	122x83x15 mm
Part number:	05078626001	Weight:	56 g
Article number:	7771	Country of origin:	TW
		Customs tariff number:	82079099

- Square head insert tool 9x12 mm
- For torque wrenches from the Click-Torque X series with 9x12 mm mounting
- Application: Hexagon screw heads or nuts
- With safety pin
- The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads

Ring spanner insert, for hexagon screw heads or nuts; for torque wrenches of the Click-Torque X series with 9x12 mm holder.

Web link
<https://www.wera.de/en/05078626001>

Wera - 7771
05078626001 - 4013288196217

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Drive 9x12 mm

Chrome vanadium steel

With pin lock



For torque wrenches from the Click-Torque X series with 9x12 mm mounting.



The insert tools are suitable for high loads thanks to their chrome-vanadium steel design.



Safe working and rapid tool change thanks to the pin lock of the insert tools.

Further versions in this product family:

							
	mm	mm	mm	mm	mm	mm	mm
05078620001	9x12	7	17.5	41.3	24.7	22.5	8.0
05078621001	9x12	8	17.5	41.5	24.9	22.5	8.0
05078622001	9x12	9	17.5	41.5	24.9	22.5	9.0
05078623001	9x12	10	17.5	43.0	26.4	22.5	9.0
05078624001	9x12	11	17.5	43.8	27.2	22.5	9.0
05078625001	9x12	12	17.5	44.5	27.9	22.5	11.0
05078626001	9x12	13	17.5	45.1	28.5	22.5	11.0
05078627001	9x12	14	17.5	46.0	29.1	23.4	11.0
05078628001	9x12	15	17.5	46.0	29.1	23.9	12.0
05078629001	9x12	16	17.5	47.3	30.7	25.9	13
05078630001	9x12	17	17.5	47.3	30.7	27.2	13
05078631001	9x12	18	17.5	48.7	32.1	28.6	13
05078632001	9x12	19	17.5	49.2	32.6	29.5	15.0
05078633001	9x12	21	17.5	51.0	34.4	33.7	15.0

Web link
<https://www.wera.de/en/05078626001>

Wera - 7771
 05078626001 - 4013288196217

Wera Werkzeuge GmbH
 Korzelter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de