

Leather glove in full grain goatskin, winter-lined with fleece. Comfortable, warm and flexible.

TEGERA® DYNAMIC STRENGTH 7792

Learn more

WARM AND COMFORTABLE WITH FINGERTIP SENSITIVITY

Leather glove in full grain goatskin, winter-lined with fleece. Comfortable, warm and flexible with reinforced index finger and reinforced fingertips for good fingertip sensitivity. Perfect fit. Suitable for allround work.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Perfect fit
- Extra comfortable
- Warm

FUNCTIONS

- Reinforced index finger
- Reinforced fingertips

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

TEGERA® DYNAMIC STRENGTH 7792

PREVENTS RISK OF

Prevents risk of: , Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Outdoors, All-year use, Cold environments

PRIMARY AREAS OF USE

Machine operating, Building and construction, Carpentry, Installation work, Construction, Transport work, Machine driving, Warehouse work, Wood industry work, Forest work, Repair work, Sanitation, Cleaning, Service work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cold insulation gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain goatskin
BACK MATERIAL Spandex
LINING Fully lined
LINING MATERIAL Fleece
LENGTH 220-270 mm
DEXTERITY 5
COLOUR White
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Hangtag with euro slot
FASTENING Elasticated 360°
INNER MATERIAL SPECIFICATION Polyester
OUTER MATERIAL SPECIFICATION Leather, Polyester, Elastane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN 420:2003 +A1:2009

EN 388:2016 3111X

EN 511:2006 11X

ANSI 3 ABR

FEATURES

Warm lining

SIZE		ARTICLE NUMBER	EAN
7	S	7792-7	7340118345864
8	M	7792-8	7340118345956
9	L	7792-9	7340118346045
10	XL	7792-10	7340118346137
11	XXL	7792-11	7340118346229

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.