



EAN:	4013288226808	Size:	50x6x6 mm
Part number:	05060511001	Weight:	11 g
Article number:	867/4 TORX® HF	Country of origin:	CZ
		Customs tariff number:	82079030

- For TORX® socket screws
- Holding function for recessed TORX® screws
- Also suitable for Würth ASSY screws as well as Altenloh SPAX T-STAR plus screws
- 1/4" hexagon drive (Wera connecting series 1)
- Pound-thru hexagonal
- No Take it easy colour coding

Premium bits for TORX® socket screws. The TORX® HF (HF = holding function) tools developed by Wera stand out with the geometric optimization of the original TORX® profile. The clamping force resulting from the seating stress between the tip and the screw profile keeps the screws securely on the tool! Also suitable for Würth ASSY screws as well as Altenloh SPAX T-STAR plus screws. 1/4" hexagonal, suitable for holding tools as per DIN ISO 1173-F 6.3.

Web link
<https://www.wera.de/en/05060511001>

Wera - 867/4 TORX® HF
 05060511001 - 4013288226808

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Holding function for recessed TORX® screws




The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that TORX® screws made according to Camcar Innovations, Michigan, USA specifications are securely held on the tool!

Take it easy tool finder system







Depending on their size, the 867 TORX® HF bits have different coloured bands with size stamping which make the required bit quickly accessible.

Also for ASSY and SPAX T-STAR plus screws



The Wera 867/4 TX HF bits are also suitable for Würth ASSY screws as well as Altenloh SPAX T-STAR plus screws.

Further versions in this product family:

				
		mm	inch	mm
05060505001	TX 8	50	2"	3.0
05060506001	TX 10	50	2"	4.0
05060512001	TX 10	89	3 1/2"	4.0
05060507001	TX 15	50	2"	4.0
05060513001	TX 15	89	3 1/2"	4.0
05060508001	TX 20	50	2"	4.5
05060514001	TX 20	89	3 1/2"	4.5
05060509001	TX 25	50	2"	6.0
05060515001	TX 25	89	3 1/2"	6.0
05060510001	TX 30	50	2"	6.0
05060516001	TX 30	89	3 1/2"	6.0
05060511001^{1),2)}	TX 40	50	2"	-
05060517001 ^{3),2)}	TX 40	89	3 1/2"	-

1) Hexagonal blade
 2) Not Take it easy
 3) Pound-thru hexagonal

Web link
<https://www.wera.de/en/05060511001>

Wera - 867/4 TORX® HF
 05060511001 - 4013288226808

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de