

165 i PZ/S VDE Insulated screwdriver for PlusMinus screws (Pozidriv/slotted), # 2 x 100 mm



EAN:	4013288102645	Size:	205x37x37 mm
Part number:	05006191001	Weight:	88 g
Article number:	165 i PZ/S VDE	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Combination profile - Pozidriv/slotted

Wera VDE screwdriver with multi-component Kraftform Plus handle for fast and smooth work: Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer. Combination profile slotted and Pozidriv*, especially for use with terminal strips, fuse boxes, switches, relays. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. The hexagonal anti-roll protection avoids screwdrivers from rolling away annoyingly at the workplace.



Web link

<https://www.wera.de/en/05006191001>

Wera - 165 i PZ/S VDE
05006191001 - 4013288102645

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

PlusMinus screwdrivers



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Identification marking







The screw profile and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.

Web link
<https://www.wera.de/en/05006191001>

Wera - 165 i PZ/S VDE
 05006191001 - 4013288102645

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Further versions in this product family:

		 mm	 mm	 inch
05006190001	# 1	80	98	3 1/8"
05006191001	# 2	100	105	4"

Web link
<https://www.wera.de/en/05006191001>

Wera - 165 i PZ/S VDE
05006191001 - 4013288102645

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de