



EAN:	4013288187185	Size:	170x44x22 mm
Part number:	05003334001	Weight:	40 g
Article number:	8740 A HF	Country of origin:	CZ
		Customs tariff number:	82079030

- Bit socket (non-impact) for manual or machine tool operations
- The holding function holds screws securely on the tool
- With Take it easy tool finder: colour coding by size
- Knurling on lower end for more grip when used manually.
- Chrome vanadium steel, matte chrome-plated

Bit socket with 1/4" drive and holding function for particularly comfortable screwdriving with reduced risk of losing the screw when feeding it into the workpiece. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool .



Web link

<https://www.wera.de/en/05003334001>

Wera - 8740 A HF

05003334001 - 4013288187185

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Bit sockets with retaining function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

Hex-Plus



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Manual and machine sockets









The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Web link
<https://www.wera.de/en/05003334001>

Wera - 8740 A HF
05003334001 - 4013288187185

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

							
		mm	inch	mm	mm	mm	mm
05003332001	leuchtpink_232 C	3.0	-	28.0	12.0	12.5	11.0
05003333001	gelb_123C	4.0	-	28.0	12.0	12.5	11.0
05003334001	gelb_123C	4.0	-	100.0	12.0	12.5	83.0
05003335001	leuchtorange_1 52C	5.0	-	28.0	12.0	12.5	11.0
05003336001	leuchtorange_1 52C	5.0	-	100.0	12.0	12.5	83.0
05003337001	rot_200C	6.0	-	28.0	12.0	12.5	11.0
05003338001	rot_200C	6.0	-	100.0	12.0	12.5	83.0
05003341001	violett_2735C	7.0	-	28.0	12.0	12.5	11.0
05003342001	violett_2735C	7.0	-	100.0	12.0	12.5	83.0
05003339001	pink_241C	8.0	-	28.0	12.0	12.5	11.0
05003340001	pink_241C	8.0	-	100.0	12.0	12.5	83.0
05003383001	leuchtpink_232 C	-	1/8"	28.0	12.0	12.5	11.0
05003384001	weiss	-	9/64"	28.0	12.0	12.5	11.0
05003385001	gelb_123C	-	5/32"	28.0	12.0	12.5	11.0
05003386001	leuchtorange_1 52C	-	3/16"	28.0	12.0	12.5	11.0
05003387001	rot_200C	-	7/32"	28.0	12.0	12.5	11.0
05003388001	tuerkis_339C	-	1/4"	28.0	12.0	12.5	11.0
05003389001	pink_241C	-	5/16"	28.0	12.0	12.5	11.0

Web link

<https://www.wera.de/en/05003334001>

Wera - 8740 A HF

05003334001 - 4013288187185

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de