



Swivel Sink and Pantry Faucets

B-0235-LN




TAG:

Double Pantry Faucet

Architect/Engineering Specifications:

Wall mount mixing faucet with polished chrome plated brass body, swivel outlet (less nozzle), compression cartridges with spring checks, lever handles, and 1/2" NPT adjustable female inlets. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements.

Job Name _____
 Model Specified _____ Quantity _____
 Variations Specified _____
 Date _____



Features & Benefits:

- Adjustable wall mount mixing faucet with polished chrome plated brass body
- Swivel outlet accepts T&S swing nozzles
- Lock washer included for rigid nozzle applications
- Quarter-turn Eterna compression cartridges w/ spring checks to prevent crossflow of water
- Lever handle w/ color coded indexes
- 1/2" NPT female eccentric inlets w/ Ø 2" flanges
- Adjustable centers from 2 1/4" to 8 1/4" above and below centerline
- Material: Polished chrome plated brass body and chrome plated metal handles

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 - Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)

Warranty: One Year (Limited)

Performance Data:

- Pressure: 20 - 125 psi
 - Temperature: 40 °F - 140 °F
 - Flow Rate: 16.90 GPM @ 60 psi
- (Outlet Device &/or Final Configuration May Reduce Flow Rate)



T&S Swing Nozzles

- ☐ 059X 6" Swing Nozzle
- ☐ 060X 8" Swing Nozzle
- ☐ 061X 10" Swing Nozzle
- ☐ 062X 12" Swing Nozzle
- ☐ 063X 14" Swing Nozzle
- ☐ 064X 16" Swing Nozzle
- ☐ 065X 18" Swing Nozzle
- ☐ 066X 12" Double Joint Swing Nozzle
- ☐ 067X 15" Double Joint Swing Nozzle
- ☐ 068X 18" Double Joint Swing Nozzle
- ☐ 069X 24" Double Joint Swing Nozzle

T&S Swivel Goosenecks (D x K)

- ☐ 131X 2 13/16" x 2 9/16" Swivel Gooseneck
- ☐ 132X 2 5/8" x 5 7/16" Swivel Gooseneck
- ☐ 133X 5 11/16" x 6 1/4" Swivel Gooseneck
- ☐ 135X 8 3/4" x 5 5/8" Swivel Gooseneck

Optional Handles

- ☐ 4" Wrist Action
- ☐ Lever (Standard)
- ☐ 4-Arm

Optional Cartridges With Checks

- ☐ Quarter-Turn Cerama w/ Check Valve
- ☐ Quarter-Turn Eterna w/ Spring Check (Standard)



T&S BRASS AND BRONZE WORKS, INC.



• 2 Saddleback Cove • Travelers Rest, SC 29690
 Ph 800-476-4103 • Fax 864-834-3518
 • Simi Valley, CA • Ph 800-423-0150 • www.tsbrass.com

Date: 07/17/18