



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288037848 | <b>Size:</b>                  | 70x7x6 mm |
| <b>Part number:</b>    | 05134371001   | <b>Weight:</b>                | 15 g      |
| <b>Article number:</b> | 851/4 A PH    | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For Phillips screws
- Profiled version
- Particularly hard for semi-hard materials
- 1/4" hexagon drive (Wera connecting series 4)

High quality Wera bit for Phillips screws. It has a sharp-edged profile that ensures a dependable transfer of power between the bit and screw by breaking off the paint e.g. when screw profiles are covered in it. Extra-hard design: 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**  
<https://www.wera.de/en/05134371001>

Wera - 851/4 A PH  
05134371001 - 4013288037848

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## A-Bits



A stands for aviation. A bits are particularly hard bits with a sharp-edged profile which e.g. penetrates screw profiles full of paint (such as on fuselage panels) ensuring a dependable transfer of force between the bit and the screw.

## Further versions in this product family:

|                           |  | <br>mm | <br>inch | <br>mm |
|---------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| 05134929001               | PH 0                                                                               | 50                                                                                       | 2"                                                                                           | 3                                                                                          |
| 05134906001               | PH 0                                                                               | 70                                                                                       | 2 3/4"                                                                                       | 3                                                                                          |
| 05134907001               | PH 0                                                                               | 89                                                                                       | 3 1/2"                                                                                       | 3                                                                                          |
| 05134930001               | PH 1                                                                               | 50                                                                                       | 2"                                                                                           | 4.5                                                                                        |
| 05134370001               | PH 1                                                                               | 70                                                                                       | 2 3/4"                                                                                       | 4.5                                                                                        |
| 05134372001               | PH 1                                                                               | 89                                                                                       | 3 1/2"                                                                                       | 4.5                                                                                        |
| 05134931001               | PH 2                                                                               | 50                                                                                       | 2"                                                                                           | 6                                                                                          |
| <b>05134371001</b>        | <b>PH 2</b>                                                                        | <b>70</b>                                                                                | <b>2 3/4"</b>                                                                                | <b>6</b>                                                                                   |
| 05134373001               | PH 2                                                                               | 89                                                                                       | 3 1/2"                                                                                       | 6                                                                                          |
| 05134910001 <sup>1)</sup> | PH 2                                                                               | 152                                                                                      | 6"                                                                                           | 6                                                                                          |
| 05134911001 <sup>2)</sup> | PH 2                                                                               | 152                                                                                      | 6"                                                                                           | 6                                                                                          |
| 05134932001               | PH 3                                                                               | 50                                                                                       | 2"                                                                                           | -                                                                                          |
| 05134913001               | PH 3                                                                               | 70                                                                                       | 2 3/4"                                                                                       | 8                                                                                          |
| 05134914001               | PH 3                                                                               | 89                                                                                       | 3 1/2"                                                                                       | 8                                                                                          |
| 05134915001               | PH 3                                                                               | 152                                                                                      | 6"                                                                                           | 8                                                                                          |
| 05160983001               | PH 4                                                                               | 50                                                                                       | 2"                                                                                           | 10                                                                                         |

1) Length of drive 100 mm

2) Length of drive 20 mm

## Web link

<https://www.wera.de/en/05134371001>

Wera - 851/4 A PH

05134371001 - 4013288037848

Wera Werkzeuge GmbH

Körzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)