



| | | | |
|------------------------|---------------|-------------------------------|--------------|
| EAN: | 4013288188939 | Size: | 105x44x22 mm |
| Part number: | 05003070001 | Weight: | 50 g |
| Article number: | 8767 B HF | Country of origin: | CZ |
| | | Customs tariff number: | 82079030 |

- Bit socket (non-impact) for manual or machine tool operations
- The holding function holds screws securely on the tool
- With Take it easy tool finder: colour coding by size
- Knurling on lower end for more grip when used manually.
- Chrome vanadium steel, matte chrome-plated

Bit socket with 3/8" drive and holding function for particularly comfortable screwdriving with reduced risk of losing the screw when feeding it into the workpiece. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool .

Web link
<https://www.wera.de/en/05003070001>

Wera - 8767 B HF
05003070001 - 4013288188939

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Take it easy tool finder system

Manual and machine sockets

Bit sockets with holding function for TORX® screws



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.



The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that TORX® screws made according to Camcar Innovations, Michigan, USA specifications are securely held on the tool!

Further versions in this product family:



| | | | mm | mm | mm | mm |
|--------------------|--------------------|--------------|-------------|-------------|-------------|-------------|
| 05003059001 | leuchtgruen_375C | TX 10 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003060001 | leuchtgelb_yellowC | TX 15 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003061001 | pink_241C | TX 20 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003062001 | gelb_123C | TX 25 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003063001 | gelb_123C | TX 25 | 107.0 | 12.0 | 17.5 | 81.0 |
| 05003064001 | blau_307C | TX 27 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003065001 | blau_307C | TX 27 | 107.0 | 12.0 | 17.5 | 81.0 |
| 05003066001 | leuchtorange_152C | TX 30 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003067001 | leuchtorange_152C | TX 30 | 107.0 | 12.0 | 17.5 | 81.0 |
| 05003068001 | rot_200C | TX 40 | 35.0 | 12.0 | 17.5 | 9.0 |
| 05003069001 | rot_200C | TX 40 | 107.0 | 12.0 | 17.5 | 81.0 |
| 05003070001 | gruen_363C | TX 45 | 38.5 | 12.0 | 17.5 | 12.5 |
| 05003071001 | gruen_363C | TX 45 | 100.0 | 12.0 | 17.5 | 74.5 |
| 05003072001 | cyan_2985C | TX 50 | 38.5 | 12.0 | 17.5 | 12.5 |
| 05003073001 | cyan_2985C | TX 50 | 100.0 | 12.0 | 17.5 | 74.5 |

Web link

<https://www.wera.de/en/05003070001>

Wera - 8767 B HF

05003070001 - 4013288188939

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de