



MCR
SAFETY

Klondike (KD3)

Safety Glasses

RX Option Series

Specification Sheet

PRODUCT DESCRIPTION:

The Klondike® KD3 Magnifier features style, comfort, fit and outstanding adjustability. Not only do the temples feature a 5 position ratcheting system for a personal custom fit, but also will adjust to become longer or shorter, whatever you need! Available in 1.0, 1.5, 2.0, and 2.5 diopter strengths. Don't squint on safety, choose the best **magnifier safety glasses**, choose MCR Safety!



FEATURES:

- 1.0, 1.5, 2.0, and 2.5 diopters available
- Black matte finish
- Adjustable, 5 position ratchet action spatula temple
- Clear, Gray, and Amber lens options
- Soft comfortable nose piece

TECHNICAL DATA FOR: K3H20

Series	Klondike (KD3)	ANSI Z87+	Yes
Category	Safety Glasses	CE EN166	Yes
Scratch Resistant	Yes		
Frame Material	Nylon		
Magnifier	2.0		
Packaging	White Inner Box		
Case Pack	144	Case Weight	14.859 lb.
Case Dimensions	22.047 x 14.567 x 12.992	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
K3H10	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
K3H10G	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A
K3H15	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
K3H15A	Amber	Duramass Hard Coat	Yes	80	Black	Black	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

Klondike (KD3)

Safety Glasses

RX Option Series

Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
K3H15G	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A
K3H20	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
K3H20A	Amber	Duramass Hard Coat	Yes	80	Black	Black	N/A
K3H20G	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A
K3H25	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
K3H25G	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A
KD310	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
KD310AF	Clear	Duramass Anti-Fog	Yes	90	Black	Black	N/A
KD312	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A
KD312AF	Gray	Duramass Anti-Fog	Yes	13	Black	Black	N/A
KD313	Light Blue	Duramass Hard Coat	Yes	68	Black	Black	N/A
KD314	Amber	Duramass Hard Coat	Yes	80	Black	Black	N/A
KD319	I/O Clear Mirror	Duramass Hard Coat	Yes	36	Black	Black	N/A
KD319AF	I/O Clear Mirror	UV-AF Anti-Fog	Yes	36	Black	Black	N/A
KDRX	Clear	Uncoated	No	N/A	N/A	N/A	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved