JET

DO MORE™



JWBG-8HS
8" BENCHTOP GRINDER

COMPACT SIZE. SERIOUS GRINDING PERFORMANCE.

OVERVIEW

The JET 8" Benchtop Grinder delivers dependable grinding, sharpening, and material preparation performance for professionals, makers, mechanics, fabricators, maintenance crews, and home shop users in a compact, easy-to-place format. Built for crowded benches, garage shops, and shared workspaces, it combines 8" grinding capacity, a 1/2 HP motor, integrated LED lighting, eye shields, and adjustable tool rests in a simple, ready-to-work setup. Easy to move, easy to plug in, and backed by JET's 5-year warranty, it delivers practical capability without taking over the bench.

IDEAL FOR

- Serious Hobbyists
- Small-Shop Craftsmen
- Finish Carpenters
- Vocational & Trade Schools

THE JET ADVANTAGES

- **Portability Without Restraints.** Designed to move where the work happens, the JET 8" Benchtop Grinder is easy to reposition on crowded benches, in garage shops, or between workstations. Its 30 lb. design supports flexible placement, while standard 120V power makes setup simple almost anywhere.
- **Full Grinding Capability In A Compact Setup.** Built for smaller workspaces, this grinder delivers 8" grinding capacity without taking over the bench. A 1/2 HP motor, dual 36 and 60 grit wheels, adjustable tool rests, and integrated LED lights give users the core capability needed for everyday grinding and sharpening tasks.
- **Essential Performance At A Strong Value.** The JET 8" Benchtop Grinder combines practical performance, included safety features, and long-term confidence in a value-focused package. Eye shields, wheel guards, tool rests, LED lighting, and JET's 5-year warranty give users a ready-to-work grinder without unnecessary extras.

SEE IT IN ACTION.
VISIT JETTOOLS.COM TO LEARN MORE.

INDUSTRY-LEADING SERVICE & SUPPORT


5 YEAR WARRANTY

JWBG-8HS
8" BENCHTOP GRINDER



STOCK NO.	JT1-3161
Model No.	JWBG-8HS
HP	1/2HP
Phase	1PH
Voltage	120V
Listed FLA	4.8A
Motor Speed	3,450 RPM
Arbor Size	5/8"
Grinding Wheel Size	8"
Grinding Wheel Grits	36 and 60 Grit
Eye Shields	Included
LED Lights	Included
Base Footprint	9" x 6-1/8"
Overall Dimensions	14" x 10" x 11-3/4"
Net Weight	30 lbs.
Gross Weight	32 lbs.


AVAILABLE ACCESSORIES	STOCK NO.
36 Grit Replacement Wheel	JT9-JBG8B-018
60 Grit Replacement Wheel	JT9-JBG8B-021




EYE SHIELDS FOR SAFETY
Protects user while maintaining clear visibility.



ADJUSTABLE TOOL RESTS
Stable support for precise and consistent grinding.



DUAL GRINDING WHEELS
Coarse and fine wheels for shaping and finishing.



INTEGRATED LED WORK LIGHTS
Direct lighting on both grinding areas.



COMPACT FOOTPRINT DESIGN
Fits easily on crowded benches without disruption.

SEE IT IN ACTION.
VISIT JETTOOLS.COM TO LEARN MORE.

JET
DO MORE™