



|                        |                                         |                               |              |
|------------------------|-----------------------------------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288229151                           | <b>Size:</b>                  | 230x60x14 mm |
| <b>Part number:</b>    | 05006570001                             | <b>Weight:</b>                | 30 g         |
| <b>Article number:</b> | Kraftform Kompakt VDE 67 i TORX® TIE SB | <b>Country of origin:</b>     | CZ           |
|                        |                                         | <b>Customs tariff number:</b> | 82054000     |

- Kraftform Kompakt VDE interchangeable blade for TORX® screws
- Insulated, individually tested as per IEC 60900
- 9 mm hex drive with with entry chamfer
- Black Point tip for enhanced corrosion protection and an exact fit
- Take it easy tool finder: colour coding by profile and laser-engraved size indication
- Hexagonal anti-roll feature against rolling away

VDE blade for the Kraftform Kompakt handle/interchangeable blade system. Lightning-fast blade changes without special tools. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. The Wera Black Point tip offers fitting accuracy and optimised corrosion protection. With Take it easy tool finder: colour coding by profile and laser-engraved size indication. The hexagon anti-roll protection avoids blades from rolling away unintentionally.

#### Web link

<https://www.wera.de/en/05006570001>

Wera - Kraftform Kompakt VDE 67 i TORX® TIE SB  
05006570001 - 4013288229151

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

#### Individually tested



Testing the tool for dielectric strength at 10,000 volt gives the user the peace of mind that their tool has been tested for its most important property, insulation. Wera VDE tools are subjected to this test piece by piece which guarantees safe working at up to 1,000 volt.

#### Kraftform Kompakt VDE blades




The 157 mm length blades are suitable for Wera Kraftform bitholding screwdrivers 7400 VDE, 837 i RA, 827 T i and 817 VDE.

#### The handle/blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

#### Take it easy




The Kraftform Kompakt VDE blades are equipped with the Take it easy tool finder. Colour coding by profile and laser-engraved size indication make it easy to identify the required tool quickly.

#### Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

#### Fast turning



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.

#### Web link

<https://www.wera.de/en/05006570001>

Wera - Kraftform Kompakt VDE 67 i TORX® TIE SB  
05006570001 - 4013288229151

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Set contents:

Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm



05006534001

1x TX 10 x 157 mm



Web link

<https://www.wera.de/en/05006570001>

Wera - Kraftform Kompakt VDE 67 i TORX® TiE SB  
05006570001 - 4013288229151

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)