L. H. DOTTIE

# Carded Drill & Driver Bits

## Full Line of Drill Bits, Driver Bits and Accessories




Dottie

lhdottie.com

L. H. DOTTIE

# Carded Drill & Driver Bits

## Carded Driver Bits Tools, Replacement Bits

### Carded Bits & Tools - PC 6701

- Packed 1 Per Card
- Hardened Core For Extra Strength And Reduced Breakage
- Heat Treated To Resist Breakage And Wear
- Specially Designed To Reduce Stripping

| CAT NO | TYPE | SCREW SIZE | POINT SIZE / LENGTH | STD | UNIT |
|---|---|---|---|---|---|
| **Magnetic Hex Tools** | | | | | |
| MT8C | | #6-8 | 1/4 x 1-3/4" | 1 | Ea. Card |
| MT8LC | 1/4" | #6-8 | 1/4 x 2-9/16" | 1 | Ea. Card |
| MT10C | | #10-12 | 5/16 x 1-3/4" | 1 | Ea. Card |
| MT10LC | 5/16" | #10-12 | 5/16 x 2-9/16" | 1 | Ea. Card |
| MT38C | | 1/4" | 3/8 x 1-3/4" | 1 | Ea. Card |
| MT38LC | 3/8" | 1/4" | 3/8 x 2-9/16" | 1 | Ea. Card |

### Magnetic Bit Holder - PC 6711

| | | | | |
|---|---|---|---|---|
| MBHC | Magnetic Bit Holder | 1/4 x 3" | 1 | Ea. Card |

Note: To be used with insert bits only. Not power bits.

### Multi Drive Screw Guide Kit - PC 6712

The Multi Drive Screw Guide Kit contains the most popular screw driving bits for all your fastening jobs. Drive the most difficult lengths of screws with ease using this professionally designed tool.

| CAT NO | CONTAINS | STD | UNIT |
|---|---|---|---|
| MDSG | 1-Ea Multi Drive Screw Guide<br>1-Ea Phillips #1, #2, #3<br>1-Ea Square #1, #2<br>1-Ea Slotted #6F-#8R, #8R-10F, #10R-12R | 1 | Ea. Card |




### Nickel Plated Replacement Bits For Multi Bit Drivers- PC 6768

- Packed Two Per Card • For Multi Bit Drivers • Resists Corrosion

| CAT NO | DESCRIPTION | STD | UNIT |
|---|---|---|---|
| NBT1015C | T10 & T15 Star | 1 | Ea. Card |
| NBT2025C | T20 & T25 Star | 1 | Ea. Card |
| NBP03C | 0 & 3 Phillips | 1 | Ea. Card |
| NBP12C | 1 & 2 Phillips | 1 | Ea. Card |
| NBS03C | 0 & 3 Square Recess | 1 | Ea. Card |
| NBS12C | 1 & 2 Square Recess | 1 | Ea. Card |
| NBSL46C | 4 & 6 Slotted | 1 | Ea. Card |
| RBVC | Valve Stem Bit + 5.5 Slotted | 1 | Ea. Card |
| SA14C* | 1/4" Socket Adaptor | 1 | Ea. Card |




### Tamper Proof Replacement Bits For Multi Bit Drivers - PC 6769

- Packed Two Per Card • For Multi Bit Drivers • Resists Corrosion

| CAT NO | DESCRIPTION | STD | UNIT |
|---|---|---|---|
| RTP15C | T10 & T15 Star Pin | 1 | Ea. Card |
| RTP20C | T20 & T25 Star Pin | 1 | Ea. Card |
| RTP27C | T27 & T30 Star Pin | 1 | Ea. Card |
| RHP18C | 1/8 & 9/64 Hex Pin | 1 | Ea. Card |
| RHP532C | 5/32 & 3/16 Hex Pin | 1 | Ea. Card |
| RSP68C | 6 & 8 Spanner | 1 | Ea. Card |
| RSP12C | 10 & 12 Spanner | 1 | Ea. Card |

