

Ms. Miller Harness

Models: E570 and 570 Series

Description

The E570 Ms. Miller Harness is the only full-body harness on the market specifically designed for the female worker. The special design keeps shoulder straps at the side and away from the chest, offers better hip support, and increases comfort.

Materials

Webbing (DuraFlex®): 1 ¾", 85% Polyester, 15% Urethane Elastomer

Webbing (Non-Stretch): 1 ¾", Polyester

Elastic Keepers: Polyester, Nylon, Lycra

Thread: 6 cord bonded 3 strand polyester thread. Minimum tensile of 42 lbs

Grommets: Brass

Labels: Valeron

Label Pack: Evoprene, Nylon

Hardware

D-ring: Clear Chromate Finished Carbon Steel

Buckles: Clear Chromate Finished Carbon Steel

*All hardware meets ASTM (50) fifty-hour salt spray test requirements.

Technical

Max. Working Load: 400 lbs (181kg)

Webbing Min. Tensile: 6,000 lbs (27kN)

D-ring Min. Tensile: 5,000 lbs (22kN)

Buckle Min. Tensile: 4,000 lbs (18kN)



Certification

Meets OSHA 1910.66, 1926.104, 1926.502, ANSI A10.32, Z359.1 and CSA Z259.10-06 specifications.

SKU	Webbing	Chest Strap	Shoulder Strap	Leg Straps	Weight	Special Features
E570/URN	Green Stretch	Mating	Friction	Mating	3.4 lbs (1.5kg)	Front positioning loop / Back and leg pads / Pull-free lanyard rings
E570-7/URN	Green Stretch	Mating	Friction	Mating	4.1 lbs (1.9kg)	Front positioning loop / Back and leg pads / Pull-free lanyard rings / Side D-rings
570/UYK	Yellow Non-Stretch	Mating	Friction	Mating	3.4 lbs (1.5kg)	Front positioning loop / Back and leg pads / Pull-free lanyard rings
570-7/UYK	Yellow Non-Stretch	Mating	Friction	Mating	4.1 lbs (1.9kg)	Front positioning loop / Back and leg pads / Pull-free lanyard rings / Side D-rings

For front D-ring vest-style option, add "FD" to the corresponding harness model number (Ex. E570FD/URN). Model numbers listed are for universal size. Harnesses are also available in Xsmall/XXsmall, small/medium and XXL large by replacing the "U" in the model number with "XX/XXS", "S/M" or "XXL" (Ex. E570/S/MRN or 570/S/MYK).



Toll Free 800.873.5242 • Phone 814.432.2118 • Fax 800.892.4078 • www.millerfallprotection.com

WARNING! THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM MILLER FALL PROTECTION AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. MILLER FALL PROTECTION RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.