



EAN:	4013288229533	Size:	230x60x14 mm
Part number:	05006582001	Weight:	30 g
Article number:	Kraftform Kompakt VDE 3065 iS PZ TiE SB	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Kompakt VDE interchangeable blade suitable for Pozidriv screws
- Insulated, individually tested as per IEC 60900
- Reduced shaft diameter and integrated insulation protection
- In this way, low-lying PZ screws can be accessed and actuated
- Blades made of stainless steel to prevent extraneous rust
- Vacuum ice-hardening provides the required hardness and strength
- 9 mm hex drive with entry chamfer
- Take it easy tool finder: colour coding by profile and laser-engraved size indication

VDE stainless blades for Kraftform Kompakt handle/blade system. Lightning-fast blade changes without special tools. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. Reduced blade diameter with integrated protective insulation, low-lying screw and spring elements can be easily reached and operated. Wera's stainless steel tools are vacuum ice tempered and therefore have the hardness and strength properties required for screw connections. Industrial use is possible without restrictions. With Take it easy Tool finder: Colour coding by profile and laser-engraved size indication. The hexagon anti-roll protection avoids blades from rolling away unintentionally.

Web link
<https://www.wera.de/en/05006582001>

Wera - Kraftform Kompakt VDE 3065 iS PZ TiE SB
05006582001 - 4013288229533

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Screw stainless steel together with stainless steel!



Solution to the rust problem: screwdriving stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

Vacuum ice-hardened



The stainless steel tools from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

Individually tested



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Blades for handle



The VDE-insulated Kraftform Kompakt stainless blades are suitable for the 3817 VDE Stainless handle.

The handle/blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Reduced blade diameter for lower-lying screws




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Take it easy tool finder



The Kraftform Kompakt VDE blades are equipped with the Take it easy tool finder. Colour coding by profile and laser-engraved size indication make it easy to identify the required tool quickly.

Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

Web link

<https://www.wera.de/en/05006582001>

Wera - Kraftform Kompakt VDE 3065 iS PZ TiE SB
05006582001 - 4013288229533

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

Kraftform Kompakt VDE 3065 iS PZ Take it easy, stainless steel, PZ 1 x 157 mm



1x PZ 1 x 157 mm



Web link

<https://www.wera.de/en/05006582001>

Wera - Kraftform Kompakt VDE 3065 iS PZ TiE SB
05006582001 - 4013288229533

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de