



Project / Job Name:

Location:

Fixture Type:

Notes:

65-1334 - 50W/45W/40W/35W/30W Wattage Selectable LED Light Bar Retrofit Kit; 3000K/3500K/4000K/5000K/6500K CCT Selectable; 2-Bars; 4 Feet; 120-277 Volt; Silver Finish



GENERAL	
Company	NUVO
EA Height	1.18
EA Width	3.23
EA Length	43.31
Bulb Included	Integrated
Material	Aluminum
Fixture Type	Backlit Flat Panel
Includes	Magnetic Feet, Screws, Wire nuts
Product Notes	Default CCT setting is 4000K; Default Wattage setting is 50W.
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 1KV
Total Harmonic Distortion	<20%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Silver
Additional Info	Default CCT setting is 4000K; Default Wattage setting is 50W.
Amps	0.417-0.181/0.375-0.162/0.333-0.144/0.292-0.126/0.25-0.108A
Lens Finish	Frosted
Lens Material	Polycarbonate (PC)
Nominal Length	42.0
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	2 x 32W T8

ELECTRICAL	
CCT (Kelvin Temp)	3000K/3500K/4000K/5000K/6500K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Soft White to Daylight
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	6250L/5625L/5000L/4375L/3750L
Volts	120V-277V
Watts	50W/45W/40W/35W/30W

PHYSICAL	
Lamp Base	Integrated
Finish	SILVER
Housing Color	Silver
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle

ADDITIONAL INFO	
Warranty	5-Years
Rated For Enclosed Fixture	Yes

FEATURES	
Flicker Free	Yes

PACKAGING	
UPC	045923409875
Case Cube	1.2464
Case Height	6.89
Case Length	44.09
Case Quantity	10
Case UPC	10045923409872
Case Weight	28.0
Case Width	7.09
EA Cube	0.0955
EA Height	1.18
EA Length	43.31
EA Quantity	1
EA Weight	2.6
EA Width	3.23
Inner UPC	20045923409879
Pack Type	Kraft Box
Web Height	1.19
Web Length	41.73
Web Width	0.93

COMPLIANCE	
CA Prop 65	Lead
Dark Sky Rated	No
DLC ID	S-MRQVXP
FCC Compliant	Yes
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No