

Table 26. Auxiliary power module



Description	Catalog number
120–240 Vac input 50/60 Hz—32 Vdc output	PRTBAPMDV

**Table 27. Power relay module (automatic trip relay)—
standard frame only**



Description	Voltage	Style number
1150/1150+ trip unit	24/48 Vdc	2A11772G11
1150/1150+ trip unit	120 Vac	2A11772G12
1150/1150+ trip unit	230 Vac	2A11772G13
1150/1150+ trip unit	125 Vdc	2A11772G14

Table 28. Neutral current sensors (required for ground fault)



Ampere rating	Style number
200	9253C03H01
250	9253C03H02
300	9253C03H03
400	9253C03H04
600	9253C03H05
630	9253C03H14
800	9253C03H06
1000	9253C03H07
1200	9253C03H08
1250	9253C03H15
1600	9253C03H09
2000	9253C03H10
2500	9253C03H11
3000	9253C03H12
3200	9253C03H13
4000 ①	9253C03H10
5000 ①	9253C03H11

① Quantity of two required.

Table 29. Auxiliary current transformer kit

Ampere rating	Number of poles	Style number
800–3200	3	2A11892G01
800–3200	4	2A11892G02
4000–5000	3	2A11892G03
Auxiliary current transformer 10:1	—	5720B25G01
Auxiliary current transformer 20:1	—	5720B25G02

Table 30. Current limiting fuse kit ①

Description	Style number
MA250	2A10395G02
MA300	2A10395G03
MA400	2A10395G04
MA600	2A10395G05
MA800	2A10395G06
MB1200	2A10395G07
MB1600	2A10395G08
MB2000	2A10395G09
MD2500	2A10395G15
MD3000	2A10395G16
MD3000 with heat sinks	2A10395G17
Magnum blown fuse and trip indicator	70C1273G01


① Fuse kit includes 3 fuses and mounting hardware.

Table 31. PT modules

Description	Style number
EFA Magnum breaker, PT module replacement	2A11772G01
PT module dielectric plug	70C1067G41


Cassette (cell) attachments

Table 32. Second terminal block kit



Description	Catalog number
15 (6 point) terminal blocks and labels	MSECBK

Table 33. Secondary terminal wire kit



Description	Catalog/ style number
90 wires with terminal connectors (ampere and fasten on opposite ends)	MSECBK
30 wires—40 inch long (ampere pin—one end only)	MWK40
Secondary connection PIN (male)	73479CJ11G
Secondary connection PIN (female)	73479CK11G
Fast-on terminal	73479EIA06