



<b>EAN:</b>	4013288193438	<b>Size:</b>	102x44x22 mm
<b>Part number:</b>	05003083001	<b>Weight:</b>	36 g
<b>Article number:</b>	8740 B HF	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- Bit socket (non-impact) for manual or machine tool operations
- The holding function holds screws securely on the tool
- With Take it easy tool finder: colour coding by size
- Knurling on lower end for more grip when used manually.
- Chrome vanadium steel, matte chrome-plated

Bit socket with 3/8" drive and holding function for particularly comfortable screwdriving with reduced risk of losing the screw when feeding it into the workpiece. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool .

**Web link**

<https://www.wera.de/en/05003083001>

Wera - 8740 B HF  
05003083001 - 4013288193438

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Hex-Plus**



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

**Take it easy tool finder system**



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

**Manual and machine sockets**



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

**Bit sockets with retaining function for hexagon socket screws**









The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

**Web link**  
<https://www.wera.de/en/05003083001>

Wera - 8740 B HF  
 05003083001 - 4013288193438

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)

## Further versions in this product family:

							
		mm	inch	mm	mm	mm	mm
05003030001	leuchtpink_232 C	3.0	-	35.0	12.0	17.5	9.0
05003031001	gelb_123C	4.0	-	35.0	12.0	17.5	9.0
05003032001	gelb_123C	4.0	-	107.0	12.0	17.5	81.0
05003033001	leuchtorange_1 52C	5.0	-	35.0	12.0	17.5	9.0
05003034001	leuchtorange_1 52C	5.0	-	107.0	12.0	17.5	81.0
05003035001	rot_200C	6.0	-	35.0	12.0	17.5	9.0
05003036001	rot_200C	6.0	-	107.0	12.0	17.5	81.0
05003037001	violett_2735C	7.0	-	38.5	12.0	17.5	12.5
05003038001	violett_2735C	7.0	-	100.0	12.0	17.5	74.5
05003039001	pink_241C	8.0	-	38.5	12.0	17.5	12.5
05003040001	pink_241C	8.0	-	100.0	12.0	17.5	74.5
05003041001	weiss	9.0	-	38.5	12.0	17.5	12.5
05003042001	weiss	9.0	-	100.0	12.0	17.5	74.5
05003043001	blau_307C	10.0	-	38.5	12.0	17.5	12.5
05003044001	blau_307C	10.0	-	100.0	12.0	17.5	74.5
05003080001	leuchtpink_232 C	-	1/8"	35.0	12.0	17.5	9.0
05003081001	leuchtpink_232 C	-	1/8"	107.0	12.0	17.5	81.0
05003082001	weiss	-	9/64"	35.0	12.0	17.5	9.0
<b>05003083001</b>	<b>gelb_123C</b>	-	<b>5/32"</b>	<b>35.0</b>	<b>12.0</b>	<b>17.5</b>	<b>9.0</b>
05003084001	gelb_123C	-	5/32"	107.0	12.0	17.5	81.0
05003085001	leuchtorange_1 52C	-	3/16"	35.0	12.0	17.5	9.0
05003087001	rot_200C	-	7/32"	35.0	12.0	17.5	9.0
05003086001	leuchtorange_1 52C	-	3/16"	107.0	12.0	17.5	81.0
05003088001	rot_200C	-	7/32"	107.0	12.0	17.5	81.0
05003089001	tuerkis_339C	-	1/4"	35.0	12.0	17.5	9.0
05003090001	tuerkis_339C	-	1/4"	107.0	12.0	17.5	81.0
05003091001	pink_241C	-	5/16"	38.5	12.0	17.5	12.5
05003092001	pink_241C	-	5/16"	100.0	12.0	17.5	74.5
05003093001	blau_307C	-	3/8"	38.5	12.0	17.5	12.5
05003094001	blau_307C	-	3/8"	100.0	12.0	17.5	74.5

## Web link

<https://www.wera.de/en/05003083001>

Wera - 8740 B HF  
05003083001 - 4013288193438

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

**Web link**

<https://www.wera.de/en/05003083001>

Wera - 8740 B HF

05003083001 - 4013288193438