



## G-Tek® PolyKor® AR Seamless Knit PolyKor®/Aramid Blend Glove with Neoprene Foam Coated Grip on Palm & Fingers

- Seamless knit construction provides comfort without sacrificing dexterity
- PolyKor® blended shell with Aramid is lightweight and provides excellent dexterity, tactile sensitivity, and cut resistance while providing protection in heat resistant applications, where sparks and heat are present
- Black FR neoprene foam coating provides a secure grip in dry, wet and oily conditions, infused with thousands of tiny suction cup pockets that create a vacuum effect that dispenses fluids away on contact
- ARC Rating: ATPV 13 cal/cm2
- EN 407 tested Limited Flame Spread Level 4
- ASTM F1060-08 tested Contact Heat Resistance Level 2
- **WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Handling and Moving Heavy Materials
- Maintenance and Repair Operations
- Operating Heavy Duty Machinery and Tools



## Technical Data

|                      |                       |
|----------------------|-----------------------|
| Color                | Green                 |
| Sizes Available      | S-2XL                 |
| Packaging            | Bulk Pack             |
| Packed               | 6 Dozen/Case          |
| Case Dimensions (in) | 12.20 x 14.96 x 16.93 |
| Case Weight (lbs)    | 21.83                 |
| Country of Origin    | China                 |
| Liner Material       | PolyKor, Aramid       |
| Coating              | Neoprene              |
| Coating Color        | Black                 |
| Coating Coverage     | Palm & Fingers        |
| Grip                 | Foam                  |
| Gauge                | 13                    |
| Cuff                 | Knit Wrist            |
| Construction         | Coated Seamless Knit  |

## Performance Data

|                         |       |
|-------------------------|-------|
| Cut Level               | A4    |
| ANSI Abrasion Level     | 3     |
| ANSI Puncture Level     | 3     |
| ANSI Contact Heat Level | 2     |
| EN 388                  | 3X42D |

## Care Instructions



## SKU Information

| SKU          | COLOR | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|--------------|-------|------|--------------|----------------|----------------|
| 16-AR413/S   | Green | S    | 616314402289 | 10616314402286 | 20616314402283 |
| 16-AR413/M   | Green | M    | 616314402401 | 10616314402408 | 20616314402405 |
| 16-AR413/L   | Green | L    | 616314402326 | 10616314402323 | 20616314402320 |
| 16-AR413/XL  | Green | XL   | 616314402364 | 10616314402361 | 20616314402368 |
| 16-AR413/XXL | Green | 2XL  | 616314402449 | 10616314402446 | 20616314402443 |