



EAN:	4013288193995	Size:	96x44x21 mm
Part number:	05003748001	Weight:	53 g
Article number:	8790 HMB HF	Country of origin:	CZ
		Customs tariff number:	82042000

- Socket (non-impact) for manual or power tool operations
- The holding function holds screws securely on the tool
- With Take it easy tool finder: colour coding by size
- Chrome vanadium steel, matte chrome-plated
- Equipped with ball stop groove, knurling at lower end for better gripping

Zyklop socket with 3/8" drive and holding function for extremely convenient screwdriving with reduced risk of losing the screw when addressing the workpiece. Take it easy Tool Finder with colour coding according to size - for simple and rapid accessing of the required tool.

Web link
<https://www.wera.de/en/05003748001>

Wera - 8790 HMB HF
05003748001 - 4013288193995

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklus bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklus sockets and Zyklus bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklus bit sockets).

Manual and machine sockets








The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Sockets with retaining function for hexagon headed bolts, screws and nuts



The clamping of the screw is achieved by a twin spring loaded ball retention system. The tubing is effectively protected against mechanical wear and tear by a steel ring. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

Further versions in this product family:

						
		mm	mm	mm	mm	mm
05003740001	blau_307C	6.0	29.0	12.7	17.5	6.5
05003741001	gelb_123C	7.0	29.0	13.2	17.5	6.5
05003742001	leuchtpink_232C	8.0	29.0	14.2	17.5	6.5
05003743001	gruen_363C	9.0	29.0	15.7	17.5	6.5
05003744001	leuchtgelb_yellowC	10.0	29.0	17.0	17.5	8.0
05003745001	cyan_2985C	11.0	29.0	18.2	17.5	9.5
05003746001	schwarz_blackC	12.0	29.0	19.0	17.5	9.5
05003747001	tuerkis_339C	13.0	29.0	20.4	19.5	9.5
05003748001	pink_241C	14.0	29.0	21.5	21.5	12.5
05003749001	weiss	15.0	29.0	23.5	23.5	12.5
05003750001	violett_2735C	16.0	29.0	24.2	23.5	12.5
05003751001	rot_200C	17.0	29.0	26.0	23.5	12.5
05003752001	leuchtgruen_375C	18.0	29.0	26.5	23.5	12.5
05003753001	blau_307C	19.0	29.0	28.0	23.5	12.5

Web link

<https://www.wera.de/en/05003748001>

Wera - 8790 HMB HF
05003748001 - 4013288193995

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de