



EAN: 4013288173843
Part number: 05004019001
Article number: 8100 SA 9

Size: 205x110x60 mm
Weight: 842 g
Country of origin: CZ
Customs tariff number: 82041100

- Freely pivoting ratchet head with 5 predefined locking positions
- Fine-pitched with 72 teeth
- Small return angle of only 5°
- Free-turning sleeve for high working speeds
- With Take it easy tool finder: colour coding by size

Incredibly compact set arrangement with many tools in a minimum of space. A completely new ratchet set feeling thanks to the unique textile boxes that are very robust and durable. They can be positioned upright for tidy storage on the workshop shelf. Additional surface protection due to textile outer material. Low weight and volume for simpler mobility. Take it easy Tool Finder with colour coding according to sizes.



Web link
<https://www.wera.de/en/05004019001>

Wera - 8100 SA 9
05004019001 - 4013288173843

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop "6 in 1"




Incredibly fast Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely



The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Textile boxes



The textile boxes offer dramatically improved portability, and are space-saving to boot! This means you can now carry the same collection of tools, in a much more compact and comfortable package. The hassle of running back and forth for the right tools has now become a thing of the past. And the much lower weight of a set makes carrying more convenient than ever before. The textile box including the tool will even survive a fall undamaged.

Web link

<https://www.wera.de/en/05004019001>

Wera - 8100 SA 9
05004019001 - 4013288173843

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

8000 A Zyklop Speed Ratchet with 1/4" drive, 1/4" x 152 mm



05003500001 1x 1/4" x 152 mm



8790 HMA Zyklop 1/4" socket, 3/16" x 23 mm



05003514001	1x	3/16" x 23 mm
05003515001	1x	7/32" x 23 mm
05003516001	1x	1/4" x 23 mm
05003517001	1x	9/32" x 23 mm
05003518001	1x	5/16" x 23 mm
05003519001	1x	11/32" x 23 mm
05003520001	1x	3/8" x 23 mm
05003521001	1x	7/16" x 23 mm
05003522001	1x	1/2" x 23 mm



8794 LA Zyklop extension with free-turning sleeve, long, 1/4", 1/4" x 150 mm



05003526001 1x 1/4" x 150 mm



8794 A Zyklop wobble extension, 1/4", 1/4" x 56 mm



05003527001 1x 1/4" x 56 mm



8784 A1 Zyklop bit adaptor, 1/4", 1/4" x 37 mm



05003529001 1x 1/4" x 37 mm



851/4 TZ bits, PH 1 x 50 mm



05059805001	1x	PH 1 x 50 mm
05059810001	1x	PH 2 x 50 mm
05059815001	1x	PH 3 x 50 mm



855/4 TZ bits, PZ 1 x 50 mm



05060005001	1x	PZ 1 x 50 mm
05060010001	1x	PZ 2 x 50 mm



867/4 Z TORX® bits, TX 10 x 50 mm



05060132001	1x	TX 10 x 50 mm
05060133001	1x	TX 15 x 50 mm
05060134001	1x	TX 20 x 50 mm
05060135001	1x	TX 25 x 50 mm
05060136001	1x	TX 27 x 50 mm
05060137001	1x	TX 30 x 50 mm



840/4 Z bits, 5/32" x 50 mm



05135096001	1x	5/32" x 50 mm
05135097001	1x	3/16" x 50 mm
05135098001	1x	7/32" x 50 mm
05135099001	1x	1/4" x 50 mm



Web link

<https://www.wera.de/en/05004019001>

Wera - 8100 SA 9

05004019001 - 4013288173843

Wera Werkzeuge GmbH

Korzerter Straße 21-25


D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Hook and Loop Fastener Strip 120, 120 x 50 mm

1x 120 x 50 mm



Web link

<https://www.wera.de/en/05004019001>

Wera - 8100 SA 9

05004019001 - 4013288173843

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de