



|                        |                       |                               |           |
|------------------------|-----------------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288033284         | <b>Size:</b>                  | 50x7x6 mm |
| <b>Part number:</b>    | 05066672001           | <b>Weight:</b>                | 11 g      |
| <b>Article number:</b> | 871/4 TORQ-SET® Mplus | <b>Country of origin:</b>     | CZ        |
|                        |                       | <b>Customs tariff number:</b> | 82079030  |

- For TORQ-SET® screws
- Mplus for more breaking torque and longer service life
- 1/4" hexagon drive (Wera connecting series 4)


High quality bits for TORQ-SET® screws. The stronger flanks - when compared with the conventional TORQ-SET® profile - result in 70% more breaking torque and thereby enhanced durability whilst at the same time providing a perfect fit in the screw head. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**  
<https://www.wera.de/en/05066672001>

Wera - 871/4 TORQ-SET® Mplus  
05066672001 - 4013288033284

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## TORQ-SET® Mplus



Wera developed the Mplus profile with stronger flanks compared with tools with a conventional TORQ-SET® profile. This results in approximately 70 % extra torsional strength and greatly extends the service life of Wera Mplus tools.

## Further versions in this product family:

|                    |  |  |  |  |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    | mm                                                                                 | inch                                                                               | mm                                                                                   | inch                                                                                 |
| 05066660001        | 2                                                                                  | -                                                                                  | 50                                                                                   | 2"                                                                                   |
| 05066683001        | 2                                                                                  | -                                                                                  | 89                                                                                   | 3 1/2"                                                                               |
| 05066662001        | 3                                                                                  | -                                                                                  | 50                                                                                   | 2"                                                                                   |
| 05066684001        | 3                                                                                  | -                                                                                  | 89                                                                                   | 3 1/2"                                                                               |
| 05066664001        | 4                                                                                  | -                                                                                  | 50                                                                                   | 2"                                                                                   |
| 05066685001        | 4                                                                                  | -                                                                                  | 89                                                                                   | 3 1/2"                                                                               |
| 05066666001        | 5                                                                                  | -                                                                                  | 50                                                                                   | 2"                                                                                   |
| 05066668001        | 6                                                                                  | -                                                                                  | 50                                                                                   | 2"                                                                                   |
| 05066676001        | 6                                                                                  | -                                                                                  | 70                                                                                   | 2 3/4"                                                                               |
| 05066686001        | 6                                                                                  | -                                                                                  | 89                                                                                   | 3 1/2"                                                                               |
| 05066670001        | 8                                                                                  | -                                                                                  | 50                                                                                   | 2"                                                                                   |
| 05066678001        | 8                                                                                  | -                                                                                  | 70                                                                                   | 2 3/4"                                                                               |
| 05066687001        | 8                                                                                  | -                                                                                  | 89                                                                                   | 3 1/2"                                                                               |
| <b>05066672001</b> | <b>10</b>                                                                          | <b>-</b>                                                                           | <b>50</b>                                                                            | <b>2"</b>                                                                            |
| 05066680001        | 10                                                                                 | -                                                                                  | 70                                                                                   | 2 3/4"                                                                               |
| 05066682001        | 10                                                                                 | -                                                                                  | 89                                                                                   | 3 1/2"                                                                               |
| 05066674001        | --                                                                                 | 1/4"                                                                               | 50                                                                                   | 2"                                                                                   |
| 05221110001        | --                                                                                 | 5/16"                                                                              | 50                                                                                   | 2"                                                                                   |

## Web link

<https://www.wera.de/en/05066672001>

Wera - 871/4 TORQ-SET® Mplus  
 05066672001 - 4013288033284

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)