




GAR3904, Mech Ground Conn, Conductor to Water Pipe

By Burndy

Catalog # [GAR3904](#)

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 2-1/2" - 3-1/2" Pipe, 3/8" Stud



Features

- Cable clamp swivels at 90°, permits parallel grounding of one pipe on a 90° cable run for grounding several parallel pipes
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- Provides quality assurance to recognized industry NEC standards from an independent part

Application

For Connecting A Small To Medium Range Copper Ground Conductor To Water Pipe As Well As Structural And Reinforcing Rod Shapes, Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	2.5 - 3.5 in
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size Range	4 AWG - 4/0 AWG

Conductor - Copper Tube Std Size Range	2 1/2-3 1/2
Conductor - Copper Tube Std Size	• 2 1/2 • 3 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	165.1 mm
Dimension - Height inch	6.50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Width mm	152 mm
Dimension - Width inch	6.00 in
Dimension - B Length inch	1.75 in
Dimension - Length Overall inch	1.75 in

Force Related

Installation Torque	200 LBS/in
Recommended in-lb	

General

Material - Hardware	Galvanized Steel
Plated	N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810234037
Type	GAR3902
U Bolt Type	1033G
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810234037
UPC 14 Digit GTIN	00781810234037

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1092
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)

