



TYPE 2 CLASS C SAFETY HELMET

**SERIES H2-CH
SPECIFICATION SHEET**

PRODUCT FEATURES:

- Type 2 Class C
- Rated for top and side impact
- ABS outer shell for superior strength
- 360-Degree breathability
- Our intricately designed vent channels optimize airflow and circulation while keeping flying debris out
- High-Low temperature rated
- Adjustable ratchet
- Our engineered suspension system allows you to adjust the height, circumference, or chin strap length to have a tailor-made helmet for you
- EPS Liner for additional protection
- Multiple attachment points (visor, face shield, earmuff, lamps, etc)

TECHNICAL DATA:

HELMET

- Material
 - Shell: Acrylonitrile Butadiene Styrene (ABS)
 - Inner Foam: Expanded Polystyrene (EPS)
- Weight: 1.25lbs
- Dimensions: 11"(l) x 9"(w) x 8"(h)
- Strap: 4 Point Attachment (adjustable)
- Size: Adjustable 52-63 cm circumference
- Vent: Vented
- Slotted to fit accessories
- COO: China

SUSPENSION

- Type: Ratchet (adjustable)
- Material
 - Sweatband: PET
 - Top Pad: PET
 - Suspension Strap: Polyester Fiber
 - Chin Strap: Polyester Fiber
- Weight: 0.163lbs
- Height Adjustable: Yes
- Adjustable 52-63 cm circumference Ratchet
- COO: China



STANDARDS & COMPLIANCE:

- Type 2
- Class C
- ANSI/ISEA Z89.1-2014
- EN 12492

APPLICATIONS & CARE:

The H2 safety helmet revolutionizes safety helmets. Each feature has been engineered to maximize comfort and protection. The outer shell is made with a proprietary blend of ABS and polycarbonate giving it not only superior top and side impact protection, but also resistant to high heat, low temperatures, and scratches. The H2 Class C helmets have a 360-degree air ventilation to keep you cool in hot environments yet keeps out flying debris. Our engineered suspension system boost durability and adjustability, giving you precise control over a custom fit. Additionally, H2 can be easily customized with multiple accessories such as welding face shields, tinted visors, earmuffs, and more.

H2 Safety helmets may be cleaned with soap and warm water. The helmet should not be cleaned with any harsh chemicals, gas, or an abrasive cleaner. Store away from direct sunlight and chemicals. Do not store in extreme temperatures.



TYPE 2 CLASS C SAFETY HELMET
SERIES H2-CH
SPECIFICATION SHEET

Packaging and Logistics Information

SKU	HELMET COLOR	CASE QTY	CASE WT	UPC
H2-CH-01	White	10 pcs	18 lbs	069165846687
H2-CH-02	Yellow	10 pcs	18 lbs	069165846694
H2-CH-03	Blue	10 pcs	18 lbs	069165846700
H2-CH-04	Red	10 pcs	18 lbs	069165846717
H2-CH-05	Orange	10 pcs	18 lbs	069165846724
H2-CH-06	Black	10 pcs	18 lbs	069165846731
H2-CH-07	Safety Yellow	10 pcs	18 lbs	069165846748
H2-CH-09	Pink	10 pcs	18 lbs	069165846755
H2-CH-08	Gray	10 pcs	18 lbs	069165846762

Defender Safety® and TM are trademarks owned by Defender Safety or one of its affiliates. © 2019 Defender Safety Limited. All Rights Reserved. Neither this document nor any other statement made herein by or on behalf of Defender Safety should be construed as a warranty of merchantability or that any Defender Safety product is fit for a particular purpose. Defender Safety assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.