



Kut Gard® 2-Ply Aramid Sleeve

- Aramid provides excellent cut protection and heat resistance for the wrists and arms
- Aramid fiber blend is inherently flame resistant, sleeves can withstand heat up to 640° F (337°C) without supporting a flame
- Lightweight, seamless construction for a soft and comfortable feel
- Launderable for extended life and to reduce replacement costs
- Made in the USA

Applications

- Cut Resistance with Light Heat Protection
- Automotive Applications
- Glass Operations
- Light Heat Applications



Technical Data

Color	Yellow
Sizes Available	18"
Packaging	Bulk Pack
Packed	200/Case
Case Dimensions (in)	20.00 x 14.00 x 11.00
Case Weight (lbs)	17.17
Country of Origin	United States
Liner Material	Aramid
Top of Arm	Elastic Cuff
Ply	2-Ply
Construction	Seamless Knit
Certifications	TAA Compliant
Product Circularity	Reusable / Launderable

Performance Data

Cut Level	A3
ANSI Contact Heat Level	2

Care Instructions



Machine
Wash



Water Temp
40°C



Do Not
Bleach



Tumble Dry



Low Heat

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-17

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
MSK-12	Yellow	12	616314625404	10616314625401	20616314625408
MSK-10	Yellow	10"	616314625343	10616314625340	20616314625347
MSK-13	Yellow	13"	616314627170	10616314627177	20616314627174
MSK-14	Yellow	14"	616314627187	10616314627184	20616314627181
MSK-15	Yellow	15"	616314625527	10616314625524	20616314625521
MSK-18	Yellow	18"	616314625558	10616314625555	20616314625552
MSK-24	Yellow	24"	616314625701	10616314625708	20616314625705