



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288011565 | <b>Size:</b>                  | 89x7x7 mm |
| <b>Part number:</b>    | 05059480001   | <b>Weight:</b>                | 14 g      |
| <b>Article number:</b> | 800/4 Z       | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For slotted screws
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

Tough Wera bits for slotted screws, for universal use. 1/4" hexagonal, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**  
<https://www.wera.de/en/05059480001>

Wera - 800/4 Z  
05059480001 - 4013288011565

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Tough bits



Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

### Web link

<https://www.wera.de/en/05059480001>

Wera - 800/4 Z  
05059480001 - 4013288011565

## Further versions in this product family:

|                    | <br>mm | <br>mm | <br>mm | <br>inch | <br>mm |
|--------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| 05059305001        | 0.5                                                                                     | 3.0                                                                                     | 50                                                                                      | 2"                                                                                          | 3.0                                                                                       |
| 05059466001        | 0.5                                                                                     | 3.0                                                                                     | 70                                                                                      | 2 3/4"                                                                                      | 3.0                                                                                       |
| 05059307001        | 0.5                                                                                     | 4.0                                                                                     | 50                                                                                      | 2"                                                                                          | 4.0                                                                                       |
| 05059310001        | 0.6                                                                                     | 3.5                                                                                     | 50                                                                                      | 2"                                                                                          | 3.5                                                                                       |
| 05059472001        | 0.6                                                                                     | 3.5                                                                                     | 70                                                                                      | 2 3/4"                                                                                      | 3.5                                                                                       |
| 05059450001        | 0.6                                                                                     | 3.5                                                                                     | 152                                                                                     | 6"                                                                                          | 3.5                                                                                       |
| 05059315001        | 0.6                                                                                     | 4.5                                                                                     | 50                                                                                      | 2"                                                                                          | 4.5                                                                                       |
| 05059489001        | 0.6                                                                                     | 4.5                                                                                     | 89                                                                                      | 3 1/2"                                                                                      | 4.5                                                                                       |
| 05059320001        | 0.8                                                                                     | 4.0                                                                                     | 50                                                                                      | 2"                                                                                          | 4.0                                                                                       |
| 05059478001        | 0.8                                                                                     | 4.0                                                                                     | 70                                                                                      | 2 3/4"                                                                                      | 4.0                                                                                       |
| <b>05059480001</b> | <b>0.8</b>                                                                              | <b>4.0</b>                                                                              | <b>89</b>                                                                               | <b>3 1/2"</b>                                                                               | <b>4.0</b>                                                                                |
| 05059451001        | 0.8                                                                                     | 4.0                                                                                     | 152                                                                                     | 6"                                                                                          | 4.0                                                                                       |
| 05059325001        | 0.8                                                                                     | 5.5                                                                                     | 50                                                                                      | 2"                                                                                          | 5.5                                                                                       |
| 05059330001        | 1.0                                                                                     | 5.5                                                                                     | 50                                                                                      | 2"                                                                                          | 5.5                                                                                       |
| 05059486001        | 1.0                                                                                     | 5.5                                                                                     | 70                                                                                      | 2 3/4"                                                                                      | 5.5                                                                                       |
| 05059488001        | 1.0                                                                                     | 5.5                                                                                     | 89                                                                                      | 3 1/2"                                                                                      | 5.5                                                                                       |
| 05059452001        | 1.0                                                                                     | 5.5                                                                                     | 152                                                                                     | 6"                                                                                          | 5.5                                                                                       |
| 05059335001        | 1.0                                                                                     | 6.0                                                                                     | 50                                                                                      | 2"                                                                                          | 6.0                                                                                       |
| 05059337001        | 1.2                                                                                     | 6.5                                                                                     | 50                                                                                      | 2"                                                                                          | 6.2                                                                                       |
| 05059492001        | 1.2                                                                                     | 6.5                                                                                     | 70                                                                                      | 2 3/4"                                                                                      | 6.2                                                                                       |
| 05059490001        | 1.2                                                                                     | 6.5                                                                                     | 89                                                                                      | 3 1/2"                                                                                      | 6.2                                                                                       |
| 05059453001        | 1.2                                                                                     | 6.5                                                                                     | 152                                                                                     | 6"                                                                                          | 6.2                                                                                       |
| 05059340001        | 1.2                                                                                     | 8.0                                                                                     | 50                                                                                      | 2"                                                                                          | 8.0                                                                                       |
| 05059496001        | 1.2                                                                                     | 8.0                                                                                     | 89                                                                                      | 3 1/2"                                                                                      | 8.0                                                                                       |
| 05059345001        | 1.6                                                                                     | 8.0                                                                                     | 50                                                                                      | 2"                                                                                          | 8.0                                                                                       |
| 05059500001        | 1.6                                                                                     | 8.0                                                                                     | 89                                                                                      | 3 1/2"                                                                                      | 8.0                                                                                       |

## Web link

<https://www.wera.de/en/05059480001>

Wera - 800/4 Z

05059480001 - 4013288011565

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)