



Surface Protection Accessories



			Pkg.	3M UPC Number	National Stock Number
	3M™ Scotch-Weld™ Epoxy Adhesive DP190 Gray <i>Duo-Pak, 1.7 fl oz</i>	A gray, flexible, two-part adhesive that cures at room temperature and provides high-strength bond with good performance in shear and peel. Used to seal edges of urethane tape and boots to prevent attack of fluids on adhesive.	12/case	021200-22647-2	1680-01-431-3607
	3M™ Scotch-Weld™ Epoxy Adhesive 2216 B/A Gray <i>2 oz Tube Kit</i> <i>Duo-Pak, 43 ml</i>	Flexible, two-part, room temperature curing epoxy with high peel and shear strength.	6/case	021200-20351-0	8040-00-145-0019
			12/case	021200-56659-7	8040-00-145-0019
	3M™ Scotch-Weld™ EPX™ Plus II Applicator <i>W 2:1 and 1:1 Plunger Model 9170</i>	Used to dispense Scotch-Weld adhesives in duo-pak cartridges. The applicator is a low-cost, portable, self-contained metering, mixing and dispensing machine that simultaneously meters and mixes two-part adhesives as the material is applied.	10/case	021200-50004-6	5120-01-552-0154
	3M™ Scotch-Weld™ EPX™ Applicator <i>Model 9740, 50 ml metal, older style applicator</i>	Provides fast, easy manual dispensing of Scotch-Weld adhesives in handy duo-pak cartridges.	10/box 1 box/case	021200-21789-0	1680-01-431-3606
	3M™ Scotch-Weld™ EPX™ Mixing Nozzle <i>9742, 50 ml</i>	Used to dispense Scotch-Weld adhesives in duo-pak cartridges.	10/box 72/case	021200-21791-3	5120-01-425-1023
	3M™ Scotch-Weld™ EPX™ Plus II Mixing Nozzle <i>Square, Gold</i>	Cascade meter/mix nozzle for an easy squeeze of adhesive right on target. Engineered for Scotch-Weld structural adhesives in duo-paks.	12/bag 6 bags/case	021200-50008-4	5120-01-552-0155
	3M™ Protective Tape Application Solution <i>946.3 ml</i>	Pre-mixed, water-based application solution to accurately combine the materials in the preferred ratios for the desired cleaning, ease of application and performance of 3M™ Polyurethane Protective Tape and Boots. Includes yellow squeegee and spray nozzle.	1 quart/case	048011-56800-3	6810-01-544-0866

3M Surface Protection Accessories

			Pkg.	3M UPC Number	National Stock Number
	3M™ Adhesion Promoter 86A <i>Transparent, 7" x 7" packet</i> <i>1 pint can</i>	A liquid "primer" designed to be used with 3M™ Polyurethane Protective Tape and other acrylic tapes and adhesives to enhance initial adhesion in demanding situations.	5 packets/bag 1 pouch/case	021200-96361-2	8040-01-448-4791
			12 pints/case	021200-31592-3	8040-01-450-9187
	3M™ Edge Sealer ES2000 <i>Duo-Pak, 1.7 fl oz</i>	A two-part urethane sealer. It is a clear, non-yellowing, durable sealer system that provides excellent resistance to environmental exposure.	12/case	021200-96227-1	N/A
	3M™ Tape and Residue Remover	Non-solvent based product removes polyurethane protective tapes, tape residue and neoprene without damaging composite or metal surfaces.	1 gallon can 4/case	051131-35976-5	8040-01-545-9129
			16oz tub 6/case	051131-35975-8	8040-01-545-7323
	3M™ Vinyl Tape 471 <i>1" x 36 yds</i>	Tape has a vinyl backing with a rubber adhesive. Ideal for masking curved or irregular surfaces.	72/case	Blue 021200-07204-8 Yellow 021200-06410-4 Red 021200-07193-5 Green 021200-03145-8	7510-00-634-2943 7510-00-664-0473 7510-01-070-0847 7510-01-259-1400
	3M™ High Performance Cloth <i>12.5" x 14"</i>	Provides ultra cleaning power because of its knitted, interwoven construction of water- and oil-absorbing microfibers. Excellent for the removal of: compounds, polish residues, waxes, fingerprints, dust residue, abrasive residue, solvents, splatter from welding, and grease.	50/case	Blue 048011-23589-4 White 048011-23649-5 Green 048011-23650-1 Yellow 048011-23651-8 Red 048011-23652-5	N/A N/A N/A N/A N/A

For additional information:

In the U.S., call 1-800-235-2376 or fax 1-800-435-3082. For U.S. Military, call 1-866-556-5714. If you are outside of the U.S., please contact your nearest 3M office or one of the following branches:

Australia 61-2-498-9711 tel 61-2-498-9710 fax	Austria 01-86686-298 tel 01-86686-229 fax	Brazil 55 19 3838-7876 tel 55 19 3838-6892 fax	Canada 800-410-6880 ext. 6018 tel 800-263-3489 fax
China 86-21-62753535 tel 86-21-62190698 fax	Denmark 45-43-480100 tel 45-43-968596 fax	France 0810-331-300 tel 30-31-6195 fax	Germany 02131-14-2344 tel 02131-14-3647 fax
Italy 02-7035-2177 tel 02-7035-2125 fax	Japan 03-3709-8245 tel 03-3709-8743 fax	Korea 02-3771-4114 tel 02-786-7429 fax	Netherlands 31-71-5-450-272 tel 31-71-5-450-280 fax
South Africa 11-922-9111 tel 11-922-2116 fax	Spain 34-91-321-6000 tel 34-91-321-6002 fax	Switzerland 01-724-9114 tel 01-724-9068 fax	United Kingdom (0) 161-237-6174 tel (0) 161-237-3371 fax



Aerospace and Aircraft Maintenance Division

3M Center, Building 223-1N-14
St. Paul, MN 55144-1000
www.3M.com/aerospace

3M, Scotch-Weld and EPX are trademarks of 3M Company.

Printed in U.S.A.
©3M 2008
60-9700-0105-7 (4/08)