



G-Tek® KEV™

Seamless Knit A2 Kevlar® Glove with Double-Dip Nitrile Coated MicroSurface Grip on Palm & Fingers

- Seamless knit construction provides comfort without sacrificing dexterity
- Kevlar® fiber shell provides high tensile strength relative to its weight, is inherently cut resistant and will not melt, ignite or conduct electricity
- Double-Dipped Nitrile MicroSurface coatings are impermeable providing an elevated grip in dry and oily conditions, infused with thousands of tiny suction cup pockets that create a vacuum effect that dispenses fluids away on contact
- Knit Wrist helps prevent dirt and debris from entering the glove
- Color coded hems for easy size identification
- Launderable for extended life and to reduce replacement costs

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring



Technical Data

Color	Yellow
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	17.72 x 11.42 x 10.24
Case Weight (lbs)	12.13
Country of Origin	China
Liner Material	Kevlar
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	MicroSurface
Gauge	13
Cuff	Knit Wrist
Construction	Coated Seamless Knit
Product Circularity	Recycled via Terracycle Reusable / Launderable

Performance Data

Cut Level	A2
ANSI Abrasion Level	4
ANSI Puncture Level	4
ANSI Contact Heat Level	4
EN 388	4X43B

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-07

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
09-K1660/S	Yellow	S	616314096495	01616314096494	02616314096493
09-K1660/M	Yellow	M	616314096501	01616314096500	02616314096509
09-K1660/L	Yellow	L	616314096532	01616314096531	02616314096530
09-K1660/XL	Yellow	XL	616314096518	01616314096517	02616314096516
09-K1660/XXL	Yellow	2XL	616314096525	01616314096524	02616314096523