

Catalog number	Sq Ft Coverage*	Dimensions	Watts	Amps	Resistance
<b>120 V NUHEAT Mesh</b>					
N1M012	12	20" x 8 ft	139	1.2	103
N1M015	15	20" x 9 ft	170	1.4	85
N1M025	25	20" x 15 ft	300	2.5	48
N1M030	30	20" x 19 ft	344	2.9	42
N1M040	40	20" x 23 ft	442	3.7	33
N1M050	50	20" x 29 ft	563	4.7	26
N1M060	60	20" x 36 ft	720	6.0	20
N1M070	70	20" x 41 ft	809	6.7	18
N1M080	80	20" x 49 ft	947	7.9	15
N1M085	85	20" x 52 ft	1022	8.5	14
N1M095	95	20" x 58 ft	1161	9.7	12
N1M110	110	20" x 65 ft	1299	10.8	11
N1M120	120	20" x 73 ft	1461	12.2	10
<b>240 V NUHEAT Mesh</b>					
N2M015	15	20" x 9 ft	165	0.7	349
N2M020	20	20" x 13 ft	224	0.9	258
N2M025	25	20" x 16 ft	302	1.3	191
N2M035	35	20" x 21 ft	403	1.7	143
N2M045	45	20" x 28 ft	523	2.2	110
N2M055	55	20" x 32 ft	632	2.6	91
N2M065	65	20" x 39 ft	742	3.1	78
N2M070	70	20" x 43 ft	842	3.5	68
N2M085	85	20" x 52 ft	1020	4.3	57
N2M090	90	20" x 55 ft	1102	4.6	52
N2M100	100	20" x 61 ft	1211	5.0	48
N2M120	120	20" x 73 ft	1427	5.9	40
N2M135	135	20" x 82 ft	1621	6.8	36
N2M145	145	20" x 87 ft	1704	7.1	34
N2M160	160	20" x 97 ft	1914	8.0	30
N2M170	170	20" x 102 ft	2054	8.6	28
N2M190	190	20" x 117 ft	2314	9.6	25
N2M215	215	20" x 131 ft	2589	10.8	22
N2M240	240	20" x 147 ft	2905	12.1	20

\* Square foot coverage based on square room with 2" unheated border.

## ACCESSORIES

	Catalog number	Description
<b>Electric Fault Indicator</b>	AC0100	The Electric Fault Indicator is used to verify the continuity of the heating cable and the integrity of its outer jacket during the installation process. The device connects to the cold leads of the cable and if the heating cable is damaged, the alarm on the monitor will sound. The monitor can also be re-used for subsequent installations and to help troubleshoot any problems that may arise.
<b>Heating Wire Repair Kit</b>	AC0014	The Heating Wire Repair Kit is for repairing NUHEAT Mesh heating cable that has been damaged during installation.