



PosiGrip®

Seamless Knit Nylon/Spandex Glove with Nitrile Coated Foam Grip on Palm, Fingers & Knuckles, - 15 Gauge - Touchscreen

- Seamless one-piece nylon/spandex shell offers increased comfort, finger dexterity and breathability
- Foam Nitrile coatings are breathable and durable, designed with a cell structure that disperse fluids on contact for an improved grip
- Knit Wrist helps prevent dirt and debris from entering the glove
- Color coded hems for easy size identification
- Washable, resistant to chemicals, water, and ultraviolet light
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Parts and Materials
- Equipment Maintenance and Repair
- Parts Cleaning
- Fastening and Anchoring



Technical Data

Color	Gray
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	12 Dozen/Case
Case Dimensions (in)	21.00 x 12.90 x 9.20
Case Weight (lbs)	12.00
Country of Origin	Viet Nam
Liner Material	Nylon, Spandex
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm, Fingers & Knuckles
Grip	Foam
Gauge	15
Cuff	Knit Wrist
Construction	Coated Seamless Knit
Product Circularity	Reusable / Launderable

Performance Data

ANSI Abrasion Level	4
ANSI Puncture Level	2
EN 388	4131X

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-14

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
715SNFTK/S	Gray	S	662909073105	20662909073109	10662909073102
715SNFTK/M	Gray	M	662909073112	20662909073116	10662909073119
715SNFTK/L	Gray	L	662909073129	20662909073123	10662909073126
715SNFTK/XL	Gray	XL	662909073136	20662909073130	10662909073133
715SNFTK/XXL	Gray	2XL	662909073488	20662909073482	10662909073485