



Monoprice™

4K Certified High-Speed Slim HDMI® Cable – 4K60Hz, 18Gbps, HDR, Gold-Plated, Black

Your Slender Yet Powerful Link to Uncompromised Entertainment

The Monoprice™ 4K Certified High-Speed Slim HDMI® Cable delivers reliable performance in a sleek, lightweight design, making it ideal for tight spaces and clean AV setups. Officially certified to meet HDMI 2.0 specifications, this cable supports 4K resolution at 60Hz with HDR, providing crisp images, vibrant color, and smooth motion in home theater, gaming, and professional environments. With 18Gbps bandwidth, it ensures flawless transmission of high-resolution video and multi-channel audio formats, including Dolby TrueHD and DTS-HD Master Audio.

Engineered with an ultra-slim profile, gold-plated HDMI connectors, and a durable aluminum alloy shell, this cable combines style with robust signal integrity. Triple shielding minimizes electromagnetic interference for a stable, high-quality connection, while the compact design makes it perfect for wall-mounted TVs, desktop setups, or portable use. Whether streaming, gaming, or presenting, this slim HDMI cable delivers the performance and convenience you expect from Monoprice.

Lengths: 3, 4, and 6 feet

- Certified high-speed HDMI® cable ensures full compliance with HDMI 2.0 specifications
- Supports 4K resolution at 60Hz with HDR for sharp images, vibrant color, and smooth motion
- Delivers up to 18Gbps bandwidth for flawless high-resolution video and multi-channel audio
- Ultra-slim cable design is perfect for tight spaces, wall-mounted TVs, and portable setups
- Gold-plated HDMI connectors provide corrosion resistance and reliable signal transfer
- Durable aluminum alloy connector shell offers enhanced protection and a premium look
- Triple shielding reduces electromagnetic interference for clean, stable signal quality
- Ideal for home theater, gaming, streaming devices, and professional AV applications




RELIABLE 4K ULTRA HD PERFORMANCE

Experience crisp, vibrant visuals with full support for 4K resolution at 60Hz and HDR, certified to meet HDMI 2.0 standards for consistent, high-quality playback.



SPACE-SAVING SLIM DESIGN

Easily route cables behind wall-mounted TVs and monitors, as well as in tight spaces, thanks to the ultra-slim cable profile that maintains flexibility without sacrificing performance.



PREMIUM BUILD FOR LONG-TERM USE

Gold-plated connectors and durable aluminum alloy shell resist corrosion and wear, ensuring stable connections and extended cable life.

Full Specs

P/N	47912, 47913, 47914
Cable Type	Certified High-Speed HDMI Cable
HDMI Version	HDMI 2.0
Bandwidth	Up to 18 Gbps
Resolution Support	Up to 4K@60 Hz
HDR Support	HDR, DDR10, Deep Color
Audio Support	Dolby TrueHD®, DTS-HD Master Audio®
Connector Type	HDMI Type A (Standard)
Connector Shell Material	Aluminum Alloy
Cable Jacket Material	Black PVC
Shielding	Triple Shielded
Compliance	HDMI LA Certified, RoHS Compliant
Additional Features	Slim Profile for Tight Spaces
Available Lengths	3 ft, 4 ft, 6 ft
Color	Black