



PIP® Traverse™

Industrial Climbing Helmet, Type II, Non-MIPS, ABS Shell, EPS Liner, HDPE Suspension, Wheel Ratchet Adjustment, with 4-Point Chin Strap

- Ultra-lightweight shell made with ABS material provides superior protection
- EPS foam impact liner helps absorb the forces of top-of-head, front, side, and rear impacts
- Includes an adjustable 4-point cross-over chin strap with quick release buckle for a safe and secure fit
- Rugged SURE-LOCK adjustable wheel ratchet ensures proper suspension performance and fit for all head sizes
- Inner suspension includes comfortable padding for above the brow line
- Meets ANSI Z89.1-2014 Type II, Class E

Technical Data

Color	White, Black, Hi-Vis Yellow, Navy, Orange, Red, Gray, Yellow, Dark Green
Sizes Available	OS
Packaging	Boxed
Packed	18/Case
Case Dimensions (in)	28.35 x 11.61 x 30.71
Case Weight (lbs)	29.17
Country of Origin	China
Shell Material	ABS
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Suspension	Foam Cradle System
Chin Strap	4-Point Polyester
Sweatband	Polyester EVA
Size Range	53cm-63cm
Construction	Standard - Without MIPS
Certifications	ANSI/ISEA Z89.1, EN 12492

Performance Data

ANSI Type	Type II
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP1491R-11	Black	OS	616314960574	10616314960571	20616314960578
280-HP1491R-04	Dark Green	OS	616314960611	10616314960618	20616314960615
280-HP1491R-09	Gray	OS	616314960659	10616314960656	20616314960653
280-HP1491R-44	Hi-Vis Yellow	OS	616314960697	10616314960694	20616314960691
280-HP1491R-08	Navy	OS	616314960734	10616314960731	20616314960738
280-HP1491R-03	Orange	OS	616314960772	10616314960779	20616314960776
280-HP1491R-15	Red	OS	616314960819	10616314960816	20616314960813
280-HP1491R-01	White	OS	616314961137	10616314961134	20616314961131
280-HP1491R-02	Yellow	OS	616314961175	10616314961172	20616314961179