



| | | | |
|------------------------|---------------|-------------------------------|-------------|
| EAN: | 4013288120410 | Size: | 98x44x24 mm |
| Part number: | 05003561001 | Weight: | 65 g |
| Article number: | 8790 HMB | Country of origin: | TW |
| | | Customs tariff number: | 82042000 |

- 3/8" Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- With Take it easy tool finder: colour coding by size

The Wera manual and machine socket (ISO 2725 part 3) can be used in manual and machine operations. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. Slip-proof for easy grip even with oily hands. With ball stop groove. For external hexagon screws and bolts. Made of matte chrome-plated chrome-vanadium.


Web link

<https://www.wera.de/en/05003561001>

Wera - 8790 HMB
05003561001 - 4013288120410

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Manual and machine sockets



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.







Web link

<https://www.wera.de/en/05003561001>

Wera - 8790 HMB

05003561001 - 4013288120410

Further versions in this product family:

| | |  |  |  |  |  |  |
|--------------------|------------------------|---|---|---|---|---|---|
| | | mm | inch | mm | mm | mm | mm |
| 05003551001 | blau_307C | 6.0 | - | 29.0 | 10.5 | 18.0 | 12.0 |
| 05003552001 | gelb_123C | 7.0 | - | 29.0 | 11.0 | 18.0 | 12.0 |
| 05003553001 | leuchtpink_232 C | 8.0 | - | 29.0 | 12.2 | 18.0 | 12.0 |
| 05003554001 | gruen_363C | 9.0 | - | 29.0 | 13.5 | 18.0 | 12.0 |
| 05003555001 | leuchtgelb_yello wC | 10.0 | - | 29.0 | 14.5 | 18.0 | 12.0 |
| 05003556001 | cyan_2985C | 11.0 | - | 29.0 | 16.0 | 18.0 | 12.0 |
| 05003557001 | schwarz_blackC | 12.0 | - | 29.0 | 17.0 | 18.0 | 12.0 |
| 05003558001 | tuerkis_339C | 13.0 | - | 29.0 | 18.5 | 20.0 | 12.0 |
| 05003559001 | pink_241C | 14.0 | - | 29.0 | 19.5 | 22.0 | 12.0 |
| 05003560001 | weiss | 15.0 | - | 29.0 | 21.0 | 24.0 | 12.0 |
| 05003561001 | violett_2735C | 16.0 | - | 30.0 | 22.0 | 24.0 | 12.0 |
| 05003562001 | rot_200C | 17.0 | - | 30.0 | 23.5 | 24.0 | 12.0 |
| 05003563001 | leuchtgruen_37 5C | 18.0 | - | 30.0 | 24.5 | 24.0 | 18.0 |
| 05003564001 | blau_307C | 19.0 | - | 30.0 | 26.0 | 24.0 | 18.0 |
| 05003565001 | leuchtpink_232 C | 20.0 | - | 30.0 | 28.0 | 25.0 | 18.0 |
| 05003566001 | gruen_363C | 21.0 | - | 30.0 | 28.0 | 25.0 | 18.0 |
| 05003567001 | leuchtgelb_yello wC | 22.0 | - | 30.0 | 32.0 | 25.0 | 18.0 |
| 05003568001 | cyan_2985C | 24.0 | - | 32.0 | 32.0 | 25.0 | 20.0 |
| 05003569001 | leuchtgelb_yello wC | - | 1/4" | 29.0 | 11.0 | 18.0 | 12.0 |
| 05003570001 | blau_307C | - | 5/16" | 29.0 | 12.2 | 18.0 | 12.0 |
| 05003571001 | leuchtgruen_37 5C | - | 11/32" | 29.0 | 13.5 | 18.0 | 12.0 |
| 05003572001 | rot_200C | - | 3/8" | 29.0 | 14.5 | 18.0 | 12.0 |
| 05003573001 | violett_2735C | - | 7/16" | 29.0 | 16.0 | 18.0 | 12.0 |
| 05003574001 | tuerkis_339C | - | 1/2" | 29.0 | 18.5 | 20.0 | 12.0 |
| 05003575001 | pink_241C | - | 9/16" | 29.0 | 19.5 | 22.0 | 12.0 |
| 05003576001 | schwarz_blackC | - | 5/8" | 30.0 | 22.0 | 24.0 | 12.0 |
| 05003577001 | cyan_2985C | - | 11/16" | 30.0 | 23.0 | 24.0 | 18.0 |
| 05003578001 | gelb_123C | - | 3/4" | 30.0 | 26.0 | 24.0 | 18.0 |
| 05003579001 | blau_307C | - | 13/16" | 30.0 | 28.0 | 25.0 | 18.0 |
| 05003580001 | leuchtgruen_37 5C | - | 7/8" | 30.0 | 32.0 | 25.0 | 18.0 |

Web link

<https://www.wera.de/en/05003561001>

Wera - 8790 HMB

05003561001 - 4013288120410

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Web link

<https://www.wera.de/en/05003561001>

Wera - 8790 HMB

05003561001 - 4013288120410

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de