



EAN:	4013288232526	Size:	403x356x60 mm
Part number:	05150151001	Weight:	1860 g
Article number:	9751	Country of origin:	CZ
		Customs tariff number:	82054000

- Durable foam insert, each tool has its own place; two-coloured, missing tools will quickly be noticed
- High-quality, durable foam insert without chemical vapours
- 837 i RA VDE handle with ratchet functionality; for Kraffform Kompakt
- 817 VDE handle for Kraffform Kompakt interchangeable blades
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and Take it easy tool finder: colour coding by profile and laser-engraved size indication
- 14 interchangeable blades with reduced blade diameter and integrated protective insulation (iS)
- Interchangeable blades with Take it easy Tool finder: Colour coding by profile and laser-engraved size indication
- Width x height x depth: without tools 344 x 30 x 392 mm, with tools 344 x 46 x 392 mm

Durable foam insert; two-coloured for quick identification of missing parts; suitable for the Tool Rebel roller cabinet. Equipped with one 837 i RA bladeholding screwdriver for Wera Kraffform Kompakt VDE interchangeable blades; with fine-toothed ratchet integrated in the handle (40 teeth/return angle 9°), one Kraffform 817 VDE bladeholding screwdriver for Wera Kraffform Kompakt VDE interchangeable blades, 26 Wera Kraffform Kompakt VDE interchangeable blades with Take it easy Tool finder: Colour coding by profile and laser-engraved size indication.




Web link
<https://www.wera.de/en/05150151001>

Wera - 9751
 05150151001 - 4013288232526


Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Safe storage and quick overview



The tools sit securely in the foam thanks to precise contour cutouts, but are easy to remove. The carefully designed arrangement of the tools ensures space-saving storage and quick access to each tool.

Two-coloured foam insert



After removing the tool the light grey second foam becomes visible and therefore missing tools are quickly identified.

Individually tested




Safe working at voltages up to 1,000 V is guaranteed as all tools are individually tested at 10,000 V as per IEC 60900.

The 837 i RA bladeholding screwdriver with ratchet functionality




The integrated ratchet with fine toothing (40 teeth and a return angle of 9°) eases and accelerates screwdriving without having to reposition the tool.

Rapid screwdriving



The ratchet mechanism also allows fast "spinning" while screwdriving.

The 817 VDE bladeholding screwdriver




For Wera Kraftform Kompakt VDE interchangeable blades. With multi-component Kraftform handle for high working speeds and ergonomic screwdriving.

The bladeholding handles 837 i RA and 817 VDE



Both included bitholding screwdrivers have a 9 mm hexagonal mounting for Wera Kraftform Kompakt VDE interchangeable blades.

Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Set contents:

837 i RA Kraffform blade-holding handle with ratchet functionality, 9 x 115 mm

05057490001 1x 9 x 115 mm

**817 VDE Kraffform blade-holding handle, 9 x 98 mm**

05003990001 1x 9 x 98 mm

**Kraffform Kompakt VDE 62 iS Take it easy, PH 1 x 157 mm**

05006512001 1x PH 1 x 157 mm



05006513001 1x PH 2 x 157 mm

Kraffform Kompakt VDE 65 iS Take it easy, PZ 1 x 157 mm

05006526001 1x PZ 1 x 157 mm



05006527001 1x PZ 2 x 157 mm

Kraffform Kompakt VDE 62 iS PH/S Take it easy, # 1 x 157 mm

05006516001 1x # 1 x 157 mm



05006517001 1x # 2 x 157 mm

Kraffform Kompakt VDE 65 iS PZ/S Take it easy, # 1 x 157 mm

05006530001 1x # 1 x 157 mm



05006531001 1x # 2 x 157 mm

Kraffform Kompakt VDE 67 i TORX® Take it easy, TX 8 x 157 mm

05006532001 1x TX 8 x 157 mm



05006533001 1x TX 9 x 157 mm

05006534001 1x TX 10 x 157 mm

05006538001 1x TX 27 x 157 mm

05006539001 1x TX 30 x 157 mm

Kraffform Kompakt VDE 67 iS TORX® Take it easy, TX 15 x 157 mm

05006540001 1x TX 15 x 157 mm



05006541001 1x TX 20 x 157 mm

05006542001 1x TX 25 x 157 mm

Kraffform Kompakt VDE 64 i Take it easy, 2.5 x 157 mm

05006518001 1x 2.5 x 157 mm



05006519001 1x 3 x 157 mm

05006520001 1x 4 x 157 mm

05006521001 1x 5 x 157 mm

05006522001 1x 6 x 157 mm

Web link

<https://www.wera.de/en/05150151001>

Wera - 9751

05150151001 - 4013288232526

Wera Werkzeuge GmbH




Korzter Straße 21-25

D-42349 Wuppertal



Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm

	05006506001	1x	0.6 x 3.5 x 157 mm
	05006507001	1x	0.8 x 4 x 157 mm
	05006508001	1x	1 x 5.5 x 157 mm


Kraftform Kompakt VDE 60 i Take it easy, 1.2 x 6.5 x 157 mm

	05006505001	1x	1.2 x 6.5 x 157 mm
	05006500001	1x	0.4 x 2.5 x 157 mm

9851 Foam insert Kraftform Kompakt VDE set 1, empty, 344 x 30 x 392 mm

05137351001 ¹⁾	1x	344 x 30 x 392 mm
---------------------------	----	-------------------

1) Attention: The foam insert does not fit in the previous model 05501051001 of the roller cabinet.



Attention: The foam insert does not fit in the previous model 05501051001 of the roller cabinet.

Web link
<https://www.wera.de/en/05150151001>

Wera - 9751
 05150151001 - 4013288232526

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de