



G-Tek® Barracuda® Hi-Vis Seamless Knit A8 PolyKor® Blended Glove with Foam Nitrile Coated Grip on Palm & Fingers

- Polykor blended shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Seamless construction offers increased comfort and breathability
- Foam Nitrile coated palm and fingers are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Knit Wrist helps prevent dirt and debris from entering the glove
- Hi-Vis coloring makes this product very easy to see
- Color coded hems for easy size identification

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring



Technical Data

Color	Hi-Vis Green
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	12 Dozen/Case
Case Dimensions (in)	19.50 x 10.75 x 14.00
Case Weight (lbs)	21.01
Country of Origin	China
Liner Material	PolyKor
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Foam
Gauge	10
Cuff	Knit Wrist
Construction	Coated Seamless Knit
Product Circularity	Reusable / Launderable Recycled via Terracycle

Performance Data

Cut Level	A8
ANSI Abrasion Level	5
ANSI Puncture Level	4
EN 388	4543FX

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-11

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
HVG710SNF/S	Hi-Vis Green	S	662909556769	20662909556763	10662909556766
HVG710SNF/M	Hi-Vis Green	M	662909556776	20662909556770	10662909556773
HVG710SNF/L	Hi-Vis Green	L	662909556783	20662909556787	10662909556780
HVG710SNF/XL	Hi-Vis Green	XL	662909556790	20662909556794	10662909556797
HVG710SNF/2XL	Hi-Vis Green	2XL	662909556806	20662909556800	10662909556803